

# 4 IMPACT SOCKETS, BITS

IMPACT sockets, adaptors and sets

>> Page 168



Bits and accessory tools

>> Page 176



IMPACT driver and set

>> Page 185



# Applying controlled force. **STAHLWILLE IMPACT.**



Made in  
Germany

All the tools in the IMPACT product range have been designed for particularly heavy-duty work in conjunction with compressed air and electric power and impact screwdrivers. Especially in conjunction with power impact tools, they feature extremely good load-bearing capacity and very long lifetimes. The name IMPACT is a by-word in all fields of industry and the trades for leading-edge quality made by professionals for professionals.

4



## **RESILIENT.**

IMPACT sockets are made from high-grade chrome alloy steel. They are hardened in an oil bath to ensure they are normalised and non-warping, making them extremely accurate tools with very close tolerances.



## VERSATILE.

IMPACT quality is available individually or in sets. Whatever a specialist chooses for the task, the extensions, adaptors, joints and sockets will always fit – perfectly. Combine them as you need them. It's as simple as that.



## CLOSE-FITTING.

The remarkable fitting accuracy, which is due to very tight tolerances, guarantees minimum loss of force as the impact is transferred from the impact screwdriver to the socket insert and also guarantees dramatically improved durability.



## GENTLE.

The special IMPACT sockets with the plastic sleeve enable quick wheel changes while protecting sensitive light alloy rims.



## SAFE.

All IMPACT sockets have a straight-through central bore for the locking pin and a deep groove for the O-ring to improve grip. The locking pin is not under load during use.


12,5  
1/2"

DIN  
3121

ISO  
1174-2

## IMPACT sockets

• 1/2" O-drive



### 50IMP IMPACT sockets

- 1/2" O-drive
- DIN 3129/ISO 1711-2
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code            | mm        | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δg  |    |
|-----------------|-----------|----------------------|----------------------|---------|---------|-----|----|
| <b>23010008</b> | <b>8</b>  | 14.3                 | 25                   | 38      | 21.5    | 86  | 10 |
| <b>23010010</b> | <b>10</b> | 16.8                 | 25                   | 38      | 21.5    | 89  | 10 |
| <b>23010011</b> | <b>11</b> | 18.1                 | 25                   | 38      | 21.5    | 88  | 10 |
| <b>23010012</b> | <b>12</b> | 19.5                 | 25                   | 38      | 21.5    | 88  | 10 |
| <b>23010013</b> | <b>13</b> | 20.8                 | 25                   | 38      | 21.5    | 85  | 10 |
| <b>23010014</b> | <b>14</b> | 22.1                 | 25                   | 38      | 21.5    | 86  | 10 |
| <b>23010015</b> | <b>15</b> | 23.5                 | 30                   | 38      | 23      | 132 | 10 |
| <b>23010016</b> | <b>16</b> | 24.8                 | 30                   | 38      | 23      | 130 | 10 |
| <b>23010017</b> | <b>17</b> | 26.2                 | 30                   | 38      | 22.9    | 132 | 10 |
| <b>23010018</b> | <b>18</b> | 27.5                 | 30                   | 38      | 22.6    | 130 | 10 |
| <b>23010019</b> | <b>19</b> | 28.8                 | 30                   | 40      | 24.6    | 133 | 10 |
| <b>23010021</b> | <b>21</b> | 31.3                 | 30                   | 40      | 23      | 135 | 10 |
| <b>23010022</b> | <b>22</b> | 32.5                 | 30                   | 42      | 25      | 141 | 10 |
| <b>23010023</b> | <b>23</b> | 33.8                 | 30                   | 40      | 24.5    | 144 | 5  |
| <b>23010024</b> | <b>24</b> | 35                   | 30                   | 44      | 28      | 164 | 5  |
| <b>23010025</b> | <b>25</b> | 36.3                 | 30                   | 44      | 25      | 167 | 5  |
| <b>23010027</b> | <b>27</b> | 38.8                 | 30                   | 45      | 29      | 190 | 5  |
| <b>23010030</b> | <b>30</b> | 42                   | 30                   | 50      | 34      | 199 | 5  |
| <b>23010032</b> | <b>32</b> | 44                   | 30                   | 50      | 34      | 210 | 5  |

### 50IMP/6/2 IMPACT set

- content 12 pieces:  
6 sockets No 50 IMP: 13; 17; 19;  
21; 22; 24 mm  
1 extension No 509/5IMP  
1 universal joint No 510IMP  
for powerdrivers  
1 each rubber ring No 5091/1 IMP,  
5091/2 IMP  
1 each connecting pin No 5092/1 IMP, 5092/2 IMP




| Code            | Δg   |   |
|-----------------|------|---|
| <b>96231101</b> | 1810 | 1 |

### TCS 50IMP/51IMP/19

- 170 x 350 x 50 mm
- 19 pieces



|                                                                                                  |                                                                                          |
|--------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------|
| Code                                                                                             | <br>g |
| <b>96838777</b>                                                                                  | 3960                                                                                     |
| <b>No</b>                                                                                        | <b>Content</b>                                                                           |
|  <b>50IMP</b> | 1/2" <b>Ø</b> 10; 13; 15; 16; 17; 18; 19; 21;<br>22; 24; 27 mm                           |
|  <b>51IMP</b> | 1/2" <b>Ø</b> 13; 15; 17; 18; 19; 21; 22;<br>24 mm                                       |

### 50D IMP IMPACT sockets

- 1/2" O--drive
- DIN 3129/ISO 1711-2
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code            | mm        | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δg  |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|-----|---|
| <b>23011032</b> | <b>32</b> | 44                   | 30                   | 50      | 27      | 251 | 5 |
| <b>23011036</b> | <b>36</b> | 49                   | 35                   | 50      | 28.5    | 313 | 1 |

### 51IMP IMPACT sockets


- 1/2" O-drive
- ISO 1711-2
- for power drivers
- extra deep
- Chrome Alloy Steel, gunmetal finish



| Code            | mm        | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δg  |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|-----|---|
| <b>23020013</b> | <b>13</b> | 20.8                 | 25                   | 85      | 68.5    | 222 | 5 |
| <b>23020015</b> | <b>15</b> | 23.5                 | 30                   | 85      | 68      | 340 | 5 |
| <b>23020016</b> | <b>16</b> | 24.8                 | 30                   | 85      | 68      | 338 | 5 |
| <b>23020017</b> | <b>17</b> | 26.2                 | 30                   | 85      | 68      | 318 | 5 |
| <b>23020018</b> | <b>18</b> | 27.5                 | 30                   | 85      | 68      | 309 | 5 |
| <b>23020019</b> | <b>19</b> | 28.8                 | 30                   | 85      | 67.5    | 292 | 5 |
| <b>23020021</b> | <b>21</b> | 31.3                 | 30                   | 85      | 66.5    | 291 | 5 |
| <b>23020022</b> | <b>22</b> | 32.5                 | 30                   | 85      | 66.5    | 323 | 5 |
| <b>23020024</b> | <b>24</b> | 35                   | 30                   | 85      | 66      | 340 | 5 |
| <b>23020027</b> | <b>27</b> | 38.8                 | 30                   | 85      | 65      | 385 | 5 |

### TCS 50IMP/19/2

- 175 x 350 x 50 mm
- 21 pieces



| Code            | Δg   |  |
|-----------------|------|--|
| <b>96838791</b> | 3055 |  |

| No              | Content                                                                      |
|-----------------|------------------------------------------------------------------------------|
| <b>50IMP</b>    | 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 23; 24; 25; 27; 30; 32 mm |
| <b>509/5IMP</b> | 1/2" O 125 mm                                                                |
| <b>510IMP</b>   | 1/2" O 68 mm                                                                 |

### TCS 54IMP/2307TX/15


- 175 x 350 x 40 mm
- 15 pieces



|                                                                                     |               |                                                                                                                             |
|-------------------------------------------------------------------------------------|---------------|-----------------------------------------------------------------------------------------------------------------------------|
|                                                                                     |               |                                        |
| Code                                                                                |               | g                                                                                                                           |
| <b>96838792</b>                                                                     |               | 1285                                                                                                                        |
|                                                                                     | <b>No</b>     | <b>Content</b>                                                                                                              |
|  | <b>54IMP</b>  | 1/2"  5; 6; 7; 8; 10; 12; 14; 17; 19 mm  |
|  | <b>2307TX</b> | 1/2"  sizes T30; T40; T45; T50; T55; T60 |

## 54IMP ● IMPACT INHEX sockets

- 1/2" O-drive
- for hexagon socket head screws
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code     | mm | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | d<br>mm | Δg<br>g |   |
|----------|----|----------------------|----------------------|---------|---------|---|
| 23050005 | 5  | 38                   | 15                   | 25      | 58      | 5 |
| 23050006 | 6  | 38                   | 15                   | 25      | 59      | 5 |
| 23050007 | 7  | 38                   | 15                   | 25      | 60      | 5 |
| 23050008 | 8  | 38                   | 15                   | 25      | 60      | 5 |
| 23050010 | 10 | 40                   | 17                   | 25      | 70      | 5 |
| 23050012 | 12 | 42                   | 19                   | 30      | 111     | 5 |
| 23050014 | 14 | 43                   | 20                   | 30      | 118     | 5 |
| 23050017 | 17 | 45                   | 22                   | 30      | 134     | 5 |
| 23050019 | 19 | 50                   | 27                   | 30      | 164     | 5 |

## 54IMP/9 IMPACT set INHEX sockets


content 13 pieces:  
5; 6; 7; 8; 10; 12; 14; 17; 19 mm  
1 each rubber ring No 5091/1 IMP,  
5091/2 IMP  
1 each connecting pin  
No 5092/1 IMP, 5092/2 IMP



| Code     | Δg<br>g |   |
|----------|---------|---|
| 96231501 | 1208    | 1 |

## 2309 ○ IMPACT sockets

- 1/2" O-drive
- for power drivers
- extra deep
- with reduced outside diameter
- Chrome Alloy Steel, gunmetal finish



| Code     | mm | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δg<br>g |   |
|----------|----|----------------------|----------------------|---------|---------|---------|---|
| 23090017 | 17 | 25.7                 | 30                   | 85      | 68      | 242     | 5 |
| 23090019 | 19 | 28.2                 | 30                   | 85      | 67.5    | 257     | 5 |
| 23090221 | 21 | 30.7                 | 30                   | 85      | 66.5    | 272     | 5 |
| 23090022 | 22 | 32                   | 30                   | 85      | 66.5    | 311     | 5 |

for wheel nuts

## ES 2309/4



- 175 x 175 x 40 mm
- 4 pieces



| Code     | Δg<br>g |
|----------|---------|
| 96838162 | 1145    |

| No   | Content                  |
|------|--------------------------|
| 2309 | 1/2" O 17; 19; 21; 22 mm |

## 2309K ○ Wheel nut sockets

- 1/2" O-drive
- with plastic sleeve
- sleeve extension protects not only wheel bolts and nuts but also the wheel and holes



| Code     | mm | L<br>mm | Ø<br>mm | Δg<br>g |   |
|----------|----|---------|---------|---------|---|
| 23091017 | 17 | 86      | 27      | 235     | 1 |
| 23091019 | 19 | 86      | 29      | 250     | 1 |
| 23091221 | 21 | 86      | 31      | 265     | 1 |

## ES 2309K/3




- 175 x 175 x 40 mm
- 3 pieces

| Code     | Δg<br>g |
|----------|---------|
| 96838260 | 800     |

| No    | Content              |
|-------|----------------------|
| 2309K | 1/2" O 17; 19; 21 mm |

## 2307TX ● IMPACT sockets


- 1/2" O-drive
- inside TORX®
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code     | size | mm   | d<br>mm | L<br>mm | Δg<br>g |   |
|----------|------|------|---------|---------|---------|---|
| 23070030 | T30  | 5.5  | 25      | 40      | 57      | 5 |
| 23070040 | T40  | 6.6  | 25      | 40      | 58      | 5 |
| 23070045 | T45  | 7.8  | 25      | 40      | 59      | 5 |
| 23070050 | T50  | 8.8  | 25      | 40      | 57      | 5 |
| 23070055 | T55  | 11.2 | 25      | 40      | 61      | 5 |
| 23070060 | T60  | 13.2 | 25      | 40      | 66      | 5 |

## 2308TX ● IMPACT sockets

- 1/2" O-drive
- external TORX®
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code     | size | mm   | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | Δg<br>g |    |
|----------|------|------|----------------------|----------------------|---------|---------|----|
| 23080010 | E10  | 9.4  | 14                   | 25                   | 38      | 67      | 10 |
| 23080012 | E12  | 11.1 | 15.9                 | 25                   | 38      | 73      | 10 |
| 23080014 | E14  | 12.9 | 17.7                 | 25                   | 38      | 73      | 10 |
| 23080016 | E16  | 14.7 | 20                   | 25                   | 38      | 77      | 10 |
| 23080018 | E18  | 16.6 | 22                   | 30                   | 38      | 115     | 10 |
| 23080020 | E20  | 18.4 | 24.5                 | 30                   | 38      | 120     | 10 |
| 23080024 | E24  | 22.1 | 30                   | 30                   | 41.2    | 149     | 10 |

12.5  
1/2"

DIN  
3121

ISO  
1174-2

4

12.5  
1/2"

20  
3/4"


DIN  
3121

ISO  
1174-2

## Accessory tools for IMPACT sockets

- 1/2" -drive
- outside E 12.5, inside G 12.5
- Finish: Chrome Alloy Steel, gunmetal finish

### 509IMP Extensions



| Code            | size      | L<br>mm | d<br>mm | Δ<br>g |   |
|-----------------|-----------|---------|---------|--------|---|
| <b>33010001</b> | <b>2</b>  | 52      | 30      | 155    | 5 |
| <b>33010002</b> | <b>5</b>  | 130     | 30      | 271    | 5 |
| <b>33010003</b> | <b>10</b> | 255     | 30      | 452    | 5 |

### 510IMP Universal joint



| Code            | L<br>mm | d<br>mm | Δ<br>g |   |
|-----------------|---------|---------|--------|---|
| <b>33020000</b> | 52      | 32      | 228    | 5 |

### 513IMP Reducing adaptor



| Code            |     |     | L<br>mm | d<br>mm | Δ<br>g |   |
|-----------------|-----|-----|---------|---------|--------|---|
| <b>33030002</b> | 1/2 | 3/8 | 37      | 30      | 109    | 5 |

### 514IMP Extending adaptor



| Code            |     |     | L<br>mm | d<br>mm | Δ<br>g |   |
|-----------------|-----|-----|---------|---------|--------|---|
| <b>33030005</b> | 1/2 | 3/4 | 49      | 30      | 174    | 5 |

### 5091 Rubber rings

| Code                               | size | Δ<br>g |    |
|------------------------------------|------|--------|----|
| <b>39011940 1IMP <sup>1)</sup></b> |      | 1      | 10 |
| <b>39012440 2IMP <sup>2)</sup></b> |      | 2      | 10 |

<sup>1)</sup> for socket 8–14 mm, TORX® sizes E10–E16, sizes T30–T60  
<sup>2)</sup> for socket 15–32 mm, TORX® sizes E18–E24 and accessories


### 5092 Connecting pins

| Code                               | size | Δ<br>g |    |
|------------------------------------|------|--------|----|
| <b>39022030 1IMP <sup>1)</sup></b> |      | 1      | 10 |
| <b>39022530 2IMP <sup>2)</sup></b> |      | 2      | 10 |

<sup>1)</sup> for socket 8–14 mm, TORX® size E10–E16, size T30–T60  
<sup>2)</sup> for socket 15–32 mm, TORX® size E18–E24 and accessories

## IMPACT sockets

- 3/4" -drive



### 55IMP IMPACT sockets

- 3/4" -drive
- DIN 3129/ISO 1711-2
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code            |           | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δ<br>g |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|--------|---|
| <b>25010017</b> | <b>17</b> | 29                   | 44                   | 48      | 23      | 365    | 5 |
| <b>25010018</b> | <b>18</b> | 30.5                 | 44                   | 48      | 23      | 345    | 5 |
| <b>25010019</b> | <b>19</b> | 32                   | 44                   | 48      | 23      | 359    | 5 |
| <b>25010021</b> | <b>21</b> | 35                   | 44                   | 50      | 25      | 375    | 5 |
| <b>25010022</b> | <b>22</b> | 36.5                 | 44                   | 50      | 25      | 377    | 5 |
| <b>25010024</b> | <b>24</b> | 39.5                 | 44                   | 50      | 24.5    | 382    | 5 |
| <b>25010027</b> | <b>27</b> | 43.5                 | 44                   | 51      | 24.5    | 387    | 5 |
| <b>25010028</b> | <b>28</b> | 45                   | 44                   | 54      | 27      | 417    | 5 |
| <b>25010029</b> | <b>29</b> | 46                   | 44                   | 54      | 26.5    | 425    | 5 |
| <b>25010030</b> | <b>30</b> | 47.4                 | 44                   | 54      | 26.5    | 438    | 2 |
| <b>25010032</b> | <b>32</b> | 49.9                 | 44                   | 54      | 26      | 456    | 2 |
| <b>25010033</b> | <b>33</b> | 51.5                 | 44                   | 54      | 25.5    | 477    | 2 |
| <b>25010034</b> | <b>34</b> | 52.4                 | 44                   | 54      | 29      | 490    | 2 |
| <b>25010036</b> | <b>36</b> | 54.9                 | 44                   | 57      | 32      | 545    | 2 |
| <b>25010038</b> | <b>38</b> | 58                   | 44                   | 58      | 33      | 600    | 2 |
| <b>25010041</b> | <b>41</b> | 57                   | 44                   | 59      | 34.5    | 500    | 1 |
| <b>25010046</b> | <b>46</b> | 67                   | 44                   | 64      | 36.5    | 746    | 1 |

### 56IMP IMPACT sockets

- 3/4" -drive
- ISO 1711-2
- for power drivers
- extra deep
- Chrome Alloy Steel, gunmetal finish



| Code            |           | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δ<br>g |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|--------|---|
| <b>25020017</b> | <b>17</b> | 32                   | 44                   | 90      | 75      | 783    | 2 |
| <b>25020019</b> | <b>19</b> | 32                   | 44                   | 90      | 75      | 780    | 2 |
| <b>25020021</b> | <b>21</b> | 35                   | 44                   | 100     | 75      | 895    | 2 |
| <b>25020022</b> | <b>22</b> | 36.5                 | 44                   | 100     | 75      | 854    | 2 |
| <b>25020024</b> | <b>24</b> | 39.5                 | 44                   | 100     | 74.5    | 838    | 2 |
| <b>25020027</b> | <b>27</b> | 43.5                 | 44                   | 100     | 72.5    | 800    | 2 |
| <b>25020030</b> | <b>30</b> | 47.4                 | 44                   | 100     | 72.5    | 860    | 2 |
| <b>25020032</b> | <b>32</b> | 49.9                 | 44                   | 100     | 72      | 922    | 2 |
| <b>25020034</b> | <b>34</b> | 52.4                 | 44                   | 100     | 71.5    | 983    | 2 |
| <b>25020036</b> | <b>36</b> | 54.9                 | 44                   | 100     | 71      | 1038   | 2 |
| <b>25020041</b> | <b>41</b> | 54.9                 | 44                   | 100     | 64      | 899    | 1 |
| <b>25020046</b> | <b>46</b> | 67                   | 44                   | 100     | 64      | 1340   | 1 |

### 2509 IMPACT sockets

- 3/4" -drive
- for power drivers
- extra deep
- with reduced diameter
- Chrome Alloy Steel, gunmetal finish



| Code            |           | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | Δ<br>g |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|--------|---|
| <b>25090027</b> | <b>27</b> | 40.5                 | 44                   | 100     | 72.5    | 672    | 2 |
| <b>25090030</b> | <b>30</b> | 44.3                 | 44                   | 100     | 72.5    | 728    | 2 |
| <b>25090032</b> | <b>32</b> | 46.8                 | 44                   | 100     | 72      | 778    | 2 |
| <b>25090033</b> | <b>33</b> | 48                   | 44                   | 100     | 72      | 803    | 2 |

for Trillex wheels

## Accessory tools for IMPACT sockets

- 3/4" -drive
- outside F 20, inside H 20
- Finish: Chrome Alloy Steel, gunmetal finish

### 560IMP Extensions



| Code            | size      | L<br>mm | d<br>mm | g    |   |
|-----------------|-----------|---------|---------|------|---|
| <b>35010001</b> | <b>7</b>  | 180     | 44      | 805  | 5 |
| <b>35010002</b> | <b>10</b> | 250     | 44      | 1050 | 5 |
| <b>35010003</b> | <b>13</b> | 330     | 44      | 1305 | 5 |

### 561IMP Universal joint



| Code            | L<br>mm | d<br>mm | g   |   |
|-----------------|---------|---------|-----|---|
| <b>35020000</b> | 99      | 44      | 657 | 2 |

### 568IMP Reducing adaptor



| Code            | "   | "   | L<br>mm | d<br>mm | g   |   |
|-----------------|-----|-----|---------|---------|-----|---|
| <b>35030003</b> | 3/4 | 1/2 | 56      | 44      | 335 | 5 |

### 569IMP Extending adaptor



| Code            | "   | " | L<br>mm | d<br>mm | g   |   |
|-----------------|-----|---|---------|---------|-----|---|
| <b>35030006</b> | 3/4 | 1 | 65      | 44      | 477 | 5 |

### 5591IMP Rubber ring


| Code                        | g |    |
|-----------------------------|---|----|
| <b>39013650</b>             | 3 | 10 |
| for sockets and accessories |   |    |

### 5592IMP Connecting pin

| Code                        | g |    |
|-----------------------------|---|----|
| <b>39023540</b>             | 3 | 10 |
| for sockets and accessories |   |    |

## IMPACT sockets

- 1" -drive



20  
3/4"  
25  
1"

### 60IMP IMPACT sockets

- 1" -drive
- DIN 3129/ISO 1711-2
- for power drivers
- Chrome Alloy Steel, gunmetal finish



| Code            | mm        | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | g    |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|------|---|
| <b>26010024</b> | <b>24</b> | 41.5                 | 54                   | 58      | 28      | 638  | 2 |
| <b>26010027</b> | <b>27</b> | 45                   | 54                   | 60      | 30      | 654  | 2 |
| <b>26010030</b> | <b>30</b> | 49                   | 54                   | 62      | 32      | 688  | 2 |
| <b>26010032</b> | <b>32</b> | 51.5                 | 54                   | 63      | 32      | 694  | 2 |
| <b>26010033</b> | <b>33</b> | 52.5                 | 54                   | 63      | 31.5    | 695  | 2 |
| <b>26010036</b> | <b>36</b> | 56.5                 | 54                   | 67      | 34.5    | 754  | 2 |
| <b>26010038</b> | <b>38</b> | 59                   | 54                   | 70      | 37      | 836  | 2 |
| <b>26010041</b> | <b>41</b> | 63                   | 54                   | 70      | 36.5    | 892  | 2 |
| <b>26010042</b> | <b>42</b> | 64.5                 | 54                   | 73      | 39      | 970  | 1 |
| <b>26010046</b> | <b>46</b> | 69.5                 | 54                   | 76      | 41      | 1106 | 1 |
| <b>26010050</b> | <b>50</b> | 74.5                 | 54                   | 82      | 52      | 1362 | 1 |
| <b>26010055</b> | <b>55</b> | 81                   | 54                   | 87      | 57      | 1669 | 1 |
| <b>26010060</b> | <b>60</b> | 87                   | 54                   | 91      | 61      | 1960 | 1 |
| <b>26010065</b> | <b>65</b> | 92                   | 54                   | 85      | 55      | 1678 | 1 |
| <b>26010070</b> | <b>70</b> | 96                   | 54                   | 88      | 43      | 1803 | 1 |
| <b>26010075</b> | <b>75</b> | 100                  | 86                   | 92      | 50      | 2674 | 1 |
| <b>26010080</b> | <b>80</b> | 105                  | 86                   | 97      | 55      | 2949 | 1 |

### 66IMP IMPACT sockets

- 1" -drive
- ISO 1711-2
- for power drivers
- extra deep
- Chrome Alloy Steel, gunmetal finish



| Code            | mm        | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | g    |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|------|---|
| <b>26020024</b> | <b>24</b> | 41.5                 | 54                   | 110     | 80      | 1431 | 2 |
| <b>26020027</b> | <b>27</b> | 45                   | 54                   | 110     | 80      | 1393 | 2 |
| <b>26020030</b> | <b>30</b> | 49                   | 54                   | 110     | 79.5    | 1338 | 2 |
| <b>26020032</b> | <b>32</b> | 51.5                 | 54                   | 110     | 79      | 1296 | 2 |
| <b>26020033</b> | <b>33</b> | 52.5                 | 54                   | 110     | 78.5    | 1274 | 2 |
| <b>26020036</b> | <b>36</b> | 56.5                 | 54                   | 110     | 78      | 1312 | 2 |
| <b>26020038</b> | <b>38</b> | 59                   | 54                   | 110     | 77      | 1355 | 2 |
| <b>26020041</b> | <b>41</b> | 63                   | 54                   | 110     | 76      | 1504 | 2 |
| <b>26020046</b> | <b>46</b> | 69.5                 | 54                   | 110     | 72      | 1711 | 2 |

### 2609 IMPACT sockets

- 1" -drive
- for power drivers
- extra deep
- with reduced outside diameter
- Chrome Alloy Steel, gunmetal finish



| Code            | mm        | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | g    |   |
|-----------------|-----------|----------------------|----------------------|---------|---------|------|---|
| <b>26090027</b> | <b>27</b> | 42.3                 | 54                   | 110     | 80      | 1001 | 2 |
| <b>26090030</b> | <b>30</b> | 46                   | 54                   | 110     | 79.5    | 1047 | 2 |
| <b>26090032</b> | <b>32</b> | 48.5                 | 54                   | 110     | 79      | 1015 | 2 |
| <b>26090033</b> | <b>33</b> | 49.8                 | 54                   | 110     | 78.5    | 1102 | 2 |

for wheel nuts

25  
1"

40  
1 1/2"


DIN  
3121

ISO  
1174-2

## Accessory tools for IMPACT sockets

- 1" -drive
- outside F 25, inside H 25
- Finish: Chrome Alloy Steel, gunmetal finish

### 859IMP Extensions



| Code            | size      | L<br>mm | d<br>mm | g    |   |
|-----------------|-----------|---------|---------|------|---|
| <b>36010001</b> | <b>7</b>  | 180     | 54      | 1361 | 2 |
| <b>36010002</b> | <b>13</b> | 330     | 54      | 2168 | 2 |

### 871IMP Universal joint



| Code            | L<br>mm | d<br>mm | g    |   |
|-----------------|---------|---------|------|---|
| <b>36020000</b> | 125     | 54      | 1244 | 1 |

### 865IMP Extending adaptor



| Code            | " | "     | L<br>mm | d<br>mm | g   |   |
|-----------------|---|-------|---------|---------|-----|---|
| <b>36030007</b> | 1 | 1 1/2 | 85      | 54      | 986 | 1 |

### 866IMP Reducing adaptor



| Code            | " | "   | L<br>mm | d<br>mm | g   |   |
|-----------------|---|-----|---------|---------|-----|---|
| <b>36030005</b> | 1 | 3/4 | 70      | 54      | 565 | 2 |

### 6091IMP Rubber ring

| Code            | g |    |
|-----------------|---|----|
| <b>39014850</b> | 8 | 10 |

for sockets up to 70 mm and accessories


### 6092IMP Connecting pin

| Code            | g |    |
|-----------------|---|----|
| <b>39025050</b> | 7 | 10 |

for sockets up to 70 mm and accessories

## IMPACT sockets

- 1 1/2" -drive
- to be discontinued



### 70IMP IMPACT sockets

- 1 1/2" -drive
- DIN 3129
- for power drivers
- Chrome Alloy Steel, gunmetal finish




| Code            | mm         | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | g     |   |
|-----------------|------------|----------------------|----------------------|---------|---------|-------|---|
| <b>27010055</b> | <b>55</b>  | 86                   | 86                   | 89      | 42      | 2482  | 1 |
| <b>27010060</b> | <b>60</b>  | 92                   | 86                   | 92      | 50      | 2743  | 1 |
| <b>27010065</b> | <b>65</b>  | 100                  | 86                   | 96      | 54      | 3249  | 1 |
| <b>27010070</b> | <b>70</b>  | 105                  | 86                   | 101     | 59      | 3541  | 1 |
| <b>27010075</b> | <b>75</b>  | 109                  | 86                   | 105     | 63      | 3746  | 1 |
| <b>27010080</b> | <b>80</b>  | 115                  | 86                   | 110     | 68      | 4162  | 1 |
| <b>27010085</b> | <b>85</b>  | 121                  | 86                   | 116     | 74      | 4661  | 1 |
| <b>27010090</b> | <b>90</b>  | 130                  | 86                   | 118     | 76      | 5382  | 1 |
| <b>27010095</b> | <b>95</b>  | 135                  | 127                  | 118     | 76      | 7500  | 1 |
| <b>27010100</b> | <b>100</b> | 140                  | 127                  | 125     | 83      | 8000  | 1 |
| <b>27010105</b> | <b>105</b> | 150                  | 127                  | 125     | 83      | 9000  | 1 |
| <b>27010110</b> | <b>110</b> | 155                  | 127                  | 137     | 95      | 10500 | 1 |
| <b>27010115</b> | <b>115</b> | 160                  | 127                  | 137     | 95      | 10016 | 1 |
| <b>27010120</b> | <b>120</b> | 165                  | 127                  | 145     | 103     | 12000 | 1 |

## Accessory tools for IMPACT sockets

- 1 1/2" -drive
- outside F 40, inside H 40
- Finish: Chrome Alloy Steel, gunmetal finish
- to be discontinued

### 759IMP Extensions



| Code            | size      | L<br>mm | d<br>mm | g    |   |
|-----------------|-----------|---------|---------|------|---|
| <b>37010001</b> | <b>10</b> | 254     | 86      | 5500 | 1 |
| <b>37010002</b> | <b>13</b> | 330     | 86      | 7000 | 1 |
| <b>37010003</b> | <b>15</b> | 381     | 86      | 8000 | 1 |

### 771IMP Universal joint



| Code            | L<br>mm | d<br>mm | g    |   |
|-----------------|---------|---------|------|---|
| <b>37020000</b> | 164.2   | 86      | 4197 | 1 |

## 768IMP Extending adaptor



| Code            | 1"    | 2"    | L<br>mm | d<br>mm | △<br>g |   |
|-----------------|-------|-------|---------|---------|--------|---|
| <b>37030006</b> | 1 1/2 | 2 1/2 | 93      | 86      | 3142   | 1 |

## 867IMP Reducing adaptor



| Code            | 1"    | 2" | L<br>mm | d<br>mm | △<br>g |   |
|-----------------|-------|----|---------|---------|--------|---|
| <b>36030006</b> | 1 1/2 | 1  | 111.5   | 86      | 2180   | 1 |

also for MULTIPOWER No MP300-5000 (page 233)

## 7091 Rubber rings

| Code                               | size | △<br>g |   |
|------------------------------------|------|--------|---|
| <b>39013870 1IMP <sup>1)</sup></b> |      | 15     | 1 |
| <b>39013875 2IMP <sup>2)</sup></b> |      | 20     | 1 |

<sup>1)</sup> for sockets 70IMP 55-90 mm, 60IMP 75 and 80 mm and accessories  
<sup>2)</sup> for sockets 95-120 mm

## 7092 Connecting pins

| Code                               | size | △<br>g |   |
|------------------------------------|------|--------|---|
| <b>39023870 1IMP <sup>1)</sup></b> |      | 16     | 1 |
| <b>39023875 2IMP <sup>2)</sup></b> |      | 25     | 1 |


<sup>1)</sup> for sockets 70IMP 55-90 mm, 60IMP 75 and 80 mm and accessories  
<sup>2)</sup> for sockets 95-120 mm

## IMPACT sockets

- 2 1/2" -drive
- to be discontinued

## 80IMP IMPACT sockets

- 2 1/2" -drive
- DIN 3129
- for power drivers
- Chrome Alloy Steel, gunmetal finish




| Code            | mm         | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | L<br>mm | t<br>mm | △<br>g |   |
|-----------------|------------|----------------------|----------------------|---------|---------|--------|---|
| <b>28010075</b> | <b>75</b>  | 115                  | 127                  | 125     | 67      | 7500   | 1 |
| <b>28010080</b> | <b>80</b>  | 115                  | 127                  | 125     | 67      | 7000   | 1 |
| <b>28010085</b> | <b>85</b>  | 127                  | 127                  | 130     | 67      | 7490   | 1 |
| <b>28010090</b> | <b>90</b>  | 135                  | 127                  | 132     | 74      | 8000   | 1 |
| <b>28010095</b> | <b>95</b>  | 140                  | 127                  | 132     | 74      | 8000   | 1 |
| <b>28010100</b> | <b>100</b> | 145                  | 127                  | 141     | 83      | 9000   | 1 |
| <b>28010105</b> | <b>105</b> | 150                  | 127                  | 141     | 83      | 9000   | 1 |
| <b>28010110</b> | <b>110</b> | 160                  | 127                  | 150     | 92      | 11000  | 1 |
| <b>28010115</b> | <b>115</b> | 165                  | 127                  | 150     | 92      | 11000  | 1 |
| <b>28010120</b> | <b>120</b> | 170                  | 127                  | 158     | 100     | 12000  | 1 |

## Accessory tools for IMPACT sockets

- 2 1/2" -drive
- outside F 63, inside H 63
- Finish: Chrome Alloy Steel, gunmetal finish
- to be discontinued

## 860IMP Extensions



| Code            | size      | L<br>mm | d<br>mm | △<br>g |   |
|-----------------|-----------|---------|---------|--------|---|
| <b>38010001</b> | <b>12</b> | 315     | 127     | 16000  | 1 |
| <b>38010002</b> | <b>18</b> | 457     | 127     | 22000  | 1 |
| <b>38010003</b> | <b>24</b> | 610     | 127     | 28500  | 1 |

## 868IMP Reducing adaptor



| Code            | 1"    | 2"    | L<br>mm | d<br>mm | △<br>g |   |
|-----------------|-------|-------|---------|---------|--------|---|
| <b>38030005</b> | 2 1/2 | 1 1/2 | 145     | 27      | 7000   | 1 |

## 8091/1IMP Rubber ring

| Code            | △<br>g |   |
|-----------------|--------|---|
| <b>39016395</b> | 37     | 1 |

for sockets and accessories

## 8092/1IMP Connecting pin

| Code            | △<br>g |   |
|-----------------|--------|---|
| <b>39026397</b> | 42     | 1 |

for sockets and accessories

40  
1 1/2"

63  
2 1/2"

DIN  
3121

ISO  
1174-2

4

# Always that bit better. The STAHLWILLE range of bits.



The bit that fits – always. Because STAHLWILLE offers a wide range of drive profiles: slotted, cross-head, POZIDRIV/SUPADRIV®, female TORX®, TORX PLUS®, spline head, female hexagon drive, TRI-WING®, TORQ-SET® and female star-head screws with a centring pin. Our Made in Germany production processes, coupled with the special hardening methods and high-alloy steels, guarantee a long service life. On request, selected STAHLWILLE bits are also available in practical sets – and with the matching drive tools, such as the bit ratchet with 80 teeth and steel handle for confined working spaces.



## GRAB IT AND GO.

Ten bits in the convenient pocket-sized 1203 format – or twice that amount in the sturdy 1202 Bit Box. These compact STAHLWILLE bit boxes put the tools right where you need them. Made, of course, in Germany as premium quality tools.



## COMPACT.

Instant recognition. Arranged in sturdy plastic cases, all the most important bits and sockets are instantly accessible.



## TORSION ZONE.

Thanks to the specially developed shape of STAHlwille torsion bits, the impact from battery-powered percussion screwdrivers up to 70 N·m is absorbed, achieving a far longer service lifetime for the profile than with normal bits.

## CONVENIENT.

STAHlwille offers a particularly wide range of bits. Particularly convenient: in the event that individual bits get lost, they can easily be reordered as separate items.



Slotted



Female spline XZN®



Phillips Recess®  
(cross-head)



Internal hex



POZIDRIV®  
SUPADRIV®



TRI-WING®



Female TORX®



TORQ-SET®



Female TORX®  
with central bore



Female star-head  
with central bore



TORX PLUS®



Perfectly suited for tight spaces where manageability and efficiency are essential requirements. The steel-handled fine-tooth bit ratchet has the ideal slim, compact shape and features the special 80-tooth mechanism.



## Bits

### 1220-1223 1231-1234 Bits

- DIN 3128
- for Phillips screws



| Code     | No   | PH size |       | "    | L mm | Δ g |    |
|----------|------|---------|-------|------|------|-----|----|
| 08010000 | 1220 | 0       | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08010001 | 1221 | 1       | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08010002 | 1222 | 2       | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08010003 | 1223 | 3       | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08030001 | 1231 | 1       | C 8   | 5/16 | 32   | 9   | 10 |
| 08030002 | 1232 | 2       | C 8   | 5/16 | 32   | 10  | 10 |
| 08030003 | 1233 | 3       | C 8   | 5/16 | 32   | 10  | 10 |
| 08030004 | 1234 | 4       | C 8   | 5/16 | 32   | 12  | 10 |

outside ● DIN 3126/ISO 1173  
Phillips-Recess® DIN 5260  
extra hard for self tapping  
and other hardened screws

### PZ1221-1223 Bits

- for POZIDRIV/SUPADRIV® screws
- extra hard



| Code     | No     | PZ size |       | "   | L mm | Δ g |    |
|----------|--------|---------|-------|-----|------|-----|----|
| 08050001 | PZ1221 | 1       | C 6.3 | 1/4 | 25   | 5   | 10 |
| 08050002 | PZ1222 | 2       | C 6.3 | 1/4 | 25   | 5   | 10 |
| 08050003 | PZ1223 | 3       | C 6.3 | 1/4 | 25   | 5   | 10 |

outside ● DIN 3126/ISO 1173

### 1160-1169 Bits

- DIN 3127/ISO 2351
- for slotted screws



| Code     | No     | a x b mm   |       | "   | L mm | Δ g |    |
|----------|--------|------------|-------|-----|------|-----|----|
| 08070120 | 1160   | 0.5 x 3.0  | C 6.3 | 1/4 | 25   | 4   | 10 |
| 08070121 | 1161   | 0.5 x 4.0  | C 6.3 | 1/4 | 25   | 4   | 10 |
| 08070122 | 1162   | 0.6 x 3.5  | C 6.3 | 1/4 | 25   | 4   | 10 |
| 08070123 | 1163   | 0.6 x 4.5  | C 6.3 | 1/4 | 25   | 4   | 10 |
| 08070124 | 1164   | 0.8 x 4.0  | C 6.3 | 1/4 | 25   | 4   | 10 |
| 08070125 | 1165   | 0.8 x 5.5  | C 6.3 | 1/4 | 25   | 6   | 10 |
| 08070126 | 1166   | 1.0 x 5.5  | C 6.3 | 1/4 | 25   | 4   | 10 |
| 08070130 | 1166/1 | 1.2 x 6.5  | C 6.3 | 1/4 | 25   | 6   | 10 |
| 08070127 | 1167   | 1.2 x 8.0  | C 6.3 | 1/4 | 25   | 6   | 5  |
| 08070128 | 1168   | 1.6 x 8.0  | C 6.3 | 1/4 | 25   | 6   | 10 |
| 08070129 | 1169   | 1.6 x 10.0 | C 6.3 | 1/4 | 25   | 14  | 10 |

outside ● DIN 3126/ISO 1173

### 1350-1360 Bits

- for tri-square socket head screws (XZN®)



| Code     | No   | size |       | "    | L mm | Δ g |    |
|----------|------|------|-------|------|------|-----|----|
| 08200004 | 1350 | M4   | C 6.3 | 1/4  | 25   | 4   | 10 |
| 08200010 | 1356 | M5   | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08200011 | 1357 | M6   | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08200012 | 1358 | M8   | C 8   | 5/16 | 28   | 10  | 10 |
| 08200013 | 1359 | M10  | C 8   | 5/16 | 38   | 15  | 10 |
| 08200014 | 1360 | M12  | C 8   | 5/16 | 38   | 20  | 10 |

outside ● DIN 3126/ISO 1173  
DIN 65254 (M4, M5, M6)

Application: No 1350, size M4, for door lock attachment on the Audi TT, VW Golf, Bora, Passat B5, Lupo, New Beetle

### 1410-1421 1430-1435 Bits

- for inside TORX® screws



| Code     | No   | size | mm   |       | "    | L mm | Δ g |    |
|----------|------|------|------|-------|------|------|-----|----|
| 08130006 | 1410 | T 6  | 1.6  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130007 | 1411 | T 7  | 2.0  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130008 | 1412 | T 8  | 2.3  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130009 | 1413 | T 9  | 2.5  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130010 | 1414 | T 10 | 2.7  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130015 | 1415 | T 15 | 3.3  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130020 | 1416 | T 20 | 3.8  | C 6.3 | 1/4  | 25   | 5   | 10 |
| 08130025 | 1417 | T 25 | 4.4  | C 6.3 | 1/4  | 25   | 6   | 10 |
| 08130027 | 1418 | T 27 | 5.0  | C 6.3 | 1/4  | 25   | 6   | 10 |
| 08130030 | 1419 | T 30 | 5.5  | C 6.3 | 1/4  | 25   | 6   | 10 |
| 08130040 | 1420 | T 40 | 6.6  | C 6.3 | 1/4  | 25   | 7   | 10 |
| 08130045 | 1421 | T 45 | 7.8  | C 6.3 | 1/4  | 25   | 8   | 10 |
| 08140027 | 1430 | T 27 | 5.0  | C 8   | 5/16 | 35   | 11  | 10 |
| 08140030 | 1431 | T 30 | 5.5  | C 8   | 5/16 | 35   | 11  | 10 |
| 08140040 | 1432 | T 40 | 6.6  | C 8   | 5/16 | 35   | 12  | 10 |
| 08140045 | 1433 | T 45 | 7.8  | C 8   | 5/16 | 35   | 14  | 10 |
| 08140050 | 1434 | T 50 | 8.8  | C 8   | 5/16 | 35   | 15  | 10 |
| 08140055 | 1435 | T 55 | 11.2 | C 8   | 5/16 | 35   | 20  | 10 |

outside ● DIN 3126/ISO 1173

Application:

No 1416, size T20, for the door handle attachment for Mercedes-Benz types 168 and 203

No 1421, size T45, for removing and refitting the front doors on the VW Golf III and Vento from model year 93 on

No 1435, size T55, for screws in rear seats of BMW X6 Model E71, 7 series Model F01/F02

### 1440-1446 Bits

- with hollow point
- for inside TORX® screws (TORX® TAMPER RESISTANT)



| Code     | No   | size | mm  |       | "   | L mm | Δ g |    |
|----------|------|------|-----|-------|-----|------|-----|----|
| 08160010 | 1440 | T 10 | 2.7 | C 6.3 | 1/4 | 26   | 6   | 10 |
| 08160015 | 1441 | T 15 | 3.3 | C 6.3 | 1/4 | 26   | 6   | 10 |
| 08160020 | 1442 | T 20 | 3.8 | C 6.3 | 1/4 | 26   | 6   | 10 |
| 08160025 | 1443 | T 25 | 4.4 | C 6.3 | 1/4 | 26   | 6   | 10 |
| 08160027 | 1444 | T 27 | 5.0 | C 6.3 | 1/4 | 26   | 6   | 10 |
| 08160030 | 1445 | T 30 | 5.5 | C 6.3 | 1/4 | 26   | 6   | 10 |
| 08160040 | 1446 | T 40 | 6.6 | C 6.3 | 1/4 | 26   | 7   | 10 |

outside ● DIN 3126/ISO 1173

### 1427 Bit

- for inside TORX® screws



| Code     | size |       | "   | L mm | Δ g |   |
|----------|------|-------|-----|------|-----|---|
| 08131025 | T 25 | C 6.3 | 1/4 | 65   | 18  | 1 |

For BMW series 3 and 5

outside ● DIN 3126/ISO 1173

## 1436 IP- 1446 IP



Bits

- for inside TORX PLUS® screws



| Code       | No         |       | "   | L<br>mm | △<br>g |    |
|------------|------------|-------|-----|---------|--------|----|
| 08 16 2006 | 1436 IP 6  | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 16 2007 | 1437 IP 7  | C 6.3 | 1/4 | 25      | 4      | 10 |
| 08 16 2008 | 1438 IP 8  | C 6.3 | 1/4 | 25      | 4      | 10 |
| 08 16 2009 | 1439 IP 9  | C 6.3 | 1/4 | 25      | 4      | 10 |
| 08 16 2010 | 1440 IP 10 | C 6.3 | 1/4 | 25      | 4      | 10 |
| 08 16 2015 | 1441 IP 15 | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 16 2020 | 1442 IP 20 | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 16 2025 | 1443 IP 25 | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 16 2027 | 1444 IP 27 | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 16 2030 | 1445 IP 30 | C 6.3 | 1/4 | 25      | 6      | 10 |
| 08 16 2040 | 1446 IP 40 | C 6.3 | 1/4 | 25      | 6      | 10 |

## 1440 TPI- 1446 TPI



5-star Bits

- with hollow point
- for female 5-star screws with a centring pin



| Code       | No          |       | "   | L<br>mm | △<br>g |   |
|------------|-------------|-------|-----|---------|--------|---|
| 08 16 1010 | 1440 TPI 10 | C 6.3 | 1/4 | 26      | 6      | 5 |
| 08 16 1015 | 1441 TPI 15 | C 6.3 | 1/4 | 26      | 5      | 5 |
| 08 16 1020 | 1442 TPI 20 | C 6.3 | 1/4 | 26      | 5      | 5 |
| 08 16 1025 | 1443 TPI 25 | C 6.3 | 1/4 | 26      | 5      | 5 |
| 08 16 1027 | 1444 TPI 27 | C 6.3 | 1/4 | 26      | 5      | 5 |
| 08 16 1030 | 1445 TPI 30 | C 6.3 | 1/4 | 26      | 5      | 5 |
| 08 16 1040 | 1446 TPI 40 | C 6.3 | 1/4 | 26      | 7      | 5 |

outside ● DIN 3126/ISO 1173

## 1204/8 5-star Bit set

- storage facility for bit screwdriver inserts
- Content:
  - 1 bit-holder No 412
  - 7 bit screwdriver inserts for female 5-star screws with centring pin, sizes TPI 10, 15, 20, 25, 27, 30, 40
  - for generators, motor management units, airflow sensors, door trim, immobilisers and injection pumps (e.g. Ford, Mercedes-Benz cars & HGVs, Rover, Volvo, VW/Audi)



| Code       | △<br>g |   |
|------------|--------|---|
| 96 08 1113 | 104    | 1 |

## 1300-1304



Bits

- DIN 7426/ISO 3109
- for socket head screws
- extra hard



| Code       | No   | mm |       | "   | L<br>mm | △<br>g |    |
|------------|------|----|-------|-----|---------|--------|----|
| 08 09 0003 | 1300 | 3  | C 6.3 | 1/4 | 25      | 4      | 10 |
| 08 09 0004 | 1301 | 4  | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 09 0005 | 1302 | 5  | C 6.3 | 1/4 | 25      | 6      | 10 |
| 08 09 0006 | 1303 | 6  | C 6.3 | 1/4 | 25      | 6      | 10 |
| 08 09 0008 | 1304 | 8  | C 6.3 | 1/4 | 30      | 11     | 10 |

outside ● DIN 3126/ISO 1173

## 1299



Bit

- for inside hexagon screws
- for operating the adjusting screws on torque wrenches No 720, 721, 730 and 730N



| Code       | mm |       | "   | L<br>mm | △<br>g |    |
|------------|----|-------|-----|---------|--------|----|
| 08 09 0002 | 2  | C 6.3 | 1/4 | 34      | 4      | 10 |

outside ● DIN 3126/ISO 1173

## 13008



Bits

- for TRI-WING® screws



| Code       | TRI-WING® |       | "   | L<br>mm | △<br>g |    |
|------------|-----------|-------|-----|---------|--------|----|
| 08 25 0000 | 0         | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 25 0001 | 1         | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 25 0002 | 2         | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 25 0003 | 3         | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 25 0004 | 4         | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 25 0005 | 5         | C 6.3 | 1/4 | 25      | 5      | 10 |
| 08 25 0006 | 6         | C 6.3 | 1/4 | 25      | 8      | 10 |

outside ● DIN 3126/ISO 1173

## 13010



Bits

- for TORQ-SET® screws



| Code       | TORQ-SET® |       | "    | L<br>mm | △<br>g |    |
|------------|-----------|-------|------|---------|--------|----|
| 08 26 0000 | 0         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0001 | 1         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0002 | 2         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0003 | 3         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0004 | 4         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0005 | 5         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0006 | 6         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0008 | 8         | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0010 | 10        | C 6.3 | 1/4  | 25      | 5      | 10 |
| 08 26 0016 | 1/4       | C 8   | 5/16 | 32      | 9      | 10 |
| 08 26 0020 | 5/16      | C 8   | 5/16 | 32      | 11     | 10 |
| 08 26 0024 | 3/8       | C 8   | 5/16 | 32      | 11     | 10 |

outside ● DIN 3126/ISO 1173

## 1202

### Bit box

NEW

- storage box with screwdriver bits
  - 20 bits stored in a robust, space-saving box
  - box with internal hex drive for rapid application
- Content:
- 1 bit holder with quick-action chuck and magnet
  - ⊕ 3 bits, PH1; PH2; PH3 for Phillips screws
  - ⊕ 3 bits, PZ1; PZ2; PZ3 for POZIDRIV/SUPADRIV® screws
  - ⊖ 4 bits, sizes 0.6 x 3.5; 0.8 x 4.0; 1.0 x 5.5; 1.2 x 6.5 mm for slotted screws
  - 4 bits, sizes T15; T20; T25; T30 for inside TORX® screws
  - 3 bits, sizes T20; T25; T30 for inside TORX® screws (TORX® TAMPER RESISTANT)
  - 3 bits, sizes 4; 5; 6 mm for inside hexagon screws



Code

g

96080110

222 1

## 1203

### Bit box

NEW

- storage box with screwdriver bits
  - compact: plenty of tools - less space needed
  - incl. convenient stand-up action
- Content:
- 1 bit holder with quick-action chuck and magnet
  - ⊕ 3 bits, PH1; PH2; PH3 for Phillips screws
  - ⊕ 3 bits, PZ1; PZ2; PZ3 for POZIDRIV/SUPADRIV® screws
  - 4 bits, sizes 3; 4; 5; 6 mm for inside hexagon screws



Code

g

96080115

110 10

## 1204/21-1

### Bit box

- storage box with screwdriver bits
- Content:
- 1 magnetic bit-holder
  - ⊕ 4 bits, PH1; PH2 (2x); PH3 for Phillips screws
  - ⊕ 4 bits, PZ1; PZ2 (2x); PZ3 for POZIDRIV/SUPADRIV® screws
  - 9 bits, sizes T10; T15; T20 (2x); T25 (2x); T27; T30; T40; for inside TORX® screws
  - 3 bits, sizes 4; 5; 6 mm; for inside hexagon screws



Code

g

96080121

186 1

## 1204/21-2

### Bit box

- storage box with screwdriver bits
- Content:
- 1 magnetic bit-holder
  - ⊕ 3 bits, PH1; PH2; PH3 for Phillips screws
  - ⊖ 4 bits, sizes 0.5 x 4.0; 0.6 x 4.5; 0.8 x 5.5; 1.2 x 6.5 mm; for slotted screws
  - 6 bits, sizes T10; T15; T20; T25; T30; T40; for inside TORX® screws
  - 3 bits, sizes 4; 5; 6 mm; for inside hexagon screws
  - ⊕ 4 bits, sizes 4; 6; 8; 10 mm; for TORQ-SET® screws



Code

g


96080122

181 1

## 4000

### Spinner handles

- for bit screwdriver bits with outside hexagon 1/4"
- DIN 3126/ISO 1173 C 6.3
- handle of impact proof plastic
- internal hex drive with a collar-thrust spring
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)



Code

mm

"

d mm

L<sub>1</sub> mm

L<sub>2</sub> mm

g

18073026

D 6.3

1/4

11

75

190

119

5

inside ○ DIN 3126/ISO 1173

## 4006/1

### Spinner with magazine holder

- for 6 bit screwdriver bits (25 mm) with 1/4" outer hexagon
- DIN 3126/ISO 1173 C 6.3
- transparent plastic handle for storing bits with rotating selection cap
- internal hexagon and powerful permanent magnet



Code

mm

"

d mm

L<sub>1</sub> mm

L<sub>2</sub> mm

g

18080017

D 6.3

1/4

10

120

230

124

1

inside ○ DIN 3126/ISO 1173

## 12504

### Bit holder

- for bit screwdriver bits with outside hexagon 1/4"
- DIN 3126/ISO 1173 C 6.3
- flexible shaft



Code

mm

"

L<sub>1</sub> mm

L<sub>2</sub> mm

g

18103016

D 6.3

1/4

175

290

168

10

inside ○ DIN 3126/ISO 1173

## 12503 Bit holder

- for bit screwdriver bits with outside hexagon 1/4"
- DIN 3126/ISO 1173 C 6.3
- inside hexagon with magnet
- stubby version



| Code               | mm    | "   | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | g  |    |
|--------------------|-------|-----|----------------------|----------------------|----|----|
| <b>18 11 00 16</b> | D 6.3 | 1/4 | 10                   | 65                   | 50 | 10 |

inside DIN 3126/ISO 1173

## 4007 Bit holder

- for bit screwdriver bits with outside hexagon 1/4"
- DIN 3126/ISO 1173 C 6.3
- inside hexagon with magnet
- with T-handle



| Code               | mm    | "   | d<br>mm | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | g   |   |
|--------------------|-------|-----|---------|----------------------|----------------------|-----|---|
| <b>18 09 00 16</b> | D 6.3 | 1/4 | 10      | 200                  | 165                  | 108 | 5 |

inside DIN 3126/ISO 1173

## 415B Bit ratchet

- reversible
- 22 teeth
- with 2-component handle
- with inside hexagon 1/4"
- DIN 3126/ISO 1173 D 6.3
- for bit screwdriver sockets 1/4"
- internal hex drive with a collar-thrust spring (registered design)
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)



| Code               | L<br>mm | b<br>mm | a<br>mm | g  |   |
|--------------------|---------|---------|---------|----|---|
| <b>11 13 10 11</b> | 117     | 22      | 12      | 76 | 5 |

## 415SGB N Bit ratchet, fine tooth

FOD

- reversible
- 80 teeth
- with steel handle
- inside hexagon 1/4"
- DIN 3126/ISO 1173 D 6.3
- for bit screwdriver sockets 1/4"
- internal hex drive with a collar-thrust spring
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)
- for use in confined spaces
- re-engages after movement of 4.5°
- construction without screws prevents foreign object damage



| Code               | L<br>mm | b<br>mm | a<br>mm | g  |   |
|--------------------|---------|---------|---------|----|---|
| <b>11 13 20 20</b> | 117     | 22.6    | 10.7    | 85 | 5 |

## 418B Mini bit ratchet, fine tooth

NEW

FOD


- short model, 90 mm
- reversible
- 80 teeth
- with steel handle
- inside hexagon 1/4"
- DIN 3126/ISO 1173 D 6.3
- for bit screwdriver sockets 1/4"
- internal hex drive with a collar-thrust spring
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)
- for use in confined spaces
- re-engages after movement of 4.5°
- construction without screws prevents foreign object damage



| Code               | L<br>mm | b<br>mm | a<br>mm | g  |   |
|--------------------|---------|---------|---------|----|---|
| <b>11 13 30 30</b> | 90      | 22.5    | 11      | 70 | 1 |

## 25B Ratcheting bit holder

- reversible
- for hexagon bits
- magnetic location
- reversible heads angled
- chrome plated



| Code               | "          | L<br>mm | d <sub>1</sub><br>mm | d <sub>2</sub><br>mm | a <sub>1</sub><br>mm | a <sub>2</sub><br>mm | g   |   |
|--------------------|------------|---------|----------------------|----------------------|----------------------|----------------------|-----|---|
| <b>41 54 16 20</b> | 1/4 x 5/16 | 138     | 20                   | 23                   | 15                   | 17                   | 105 | 1 |

### Foreign Object Damage.


As safe as safe can be.



STAHLWILLE protects against foreign object damage. The preferred choice in safety-relevant fields such as aerospace, thanks to the screwless design.

### 4008 Ratcheting bit holder

- easy change of direction (anticlockwise, clockwise and fixed) by simply twisting the locking ring
- ergonomically designed, non-slip 2-component handle for optimum force transmission
- storage compartment for 6 bits in the handle; push button to open (size 1)
- for bit screwdriver inserts with external hex 1/4"
- DIN 3126/ISO 1173 Type C 6.3
- 1/4" sockets can be used with adaptor No 3115/1 (external hex and square drive 1/4")
- easy bit change thanks to internal hex. drive with magnet
- knurled spin section for faster screw advance
- heavy-duty mechanism with 48 teeth (7.5° working angle)



| Code             | size     | ○     | "   | L <sub>1</sub><br>mm | L <sub>2</sub><br>mm | d<br>mm | Δ<br>g |   |
|------------------|----------|-------|-----|----------------------|----------------------|---------|--------|---|
| <b>18 120001</b> | <b>1</b> | D 6.3 | 1/4 | 127                  | 250                  | 10      | 220    | 1 |
| <b>18 120002</b> | <b>2</b> | D 6.3 | 1/4 | 25                   | 95                   | 10      | 137    | 1 |

inside ○ DIN 3126/ISO 1173

### 4008/27/1R Ratcheting bit holder set

- in sturdy, stackable ABS plastic case
- Content 29 pieces:
- 1 ratcheting bit holder No 4008-1
  - 3 bits ⊕ 1221-1223: PH1; PH2; PH3
  - 3 bits ⊕ PZ1221-PZ1223: PZ1; PZ2; PZ3
  - 6 bits ⊕ 1440-1446: T10; T15; T20; T25; T30; T40
  - 3 bits ● 1301-1303: 4 mm; 5 mm; 6 mm
  - 3 bits ⊖ 1163 0.6 x 4.5; 1165 0.8 x 5.5; 1166/1 1.2 x 6.5 mm
  - 1 square drive extension No 3115/1 with 1/4" outer hex. and outer square drives for attaching 1/4" □
  - 9 sockets No 40, 1/4" □ 4; 5; 5.5; 6; 7; 8; 10; 11; 13 mm



| code             | Δ<br>g |   |
|------------------|--------|---|
| <b>96 182203</b> | 955    | 1 |

### Ratcheting bit holders.

Fast. Flexible. Resilient.



Thanks to their ergonomic design, they provide optimum force transmission. At the same time, they incorporate such practical features as a storage compartment for 6 bits in the handle (size 1), a knurled quick-spin section and a ratchet angle of only 7.5°.

### 1200/1 Bit holder

- with permanent magnet 1/4" inside and outside hexagon 1/4" DIN 3126/ISO 1173 C 6.3



| Code             | ○<br>mm | ●     | "   | ○<br>" | L<br>mm | Δ<br>g |   |
|------------------|---------|-------|-----|--------|---------|--------|---|
| <b>38 120001</b> | D 6.3   | E 6.3 | 1/4 | 1/4    | 72      | 37     | 5 |

inside ○/outside ● DIN 3126/ISO 1173

### 3825/1 Quick-change holder

- for bit screwdriver bits with 1/4" external hexagonal drive DIN 3126/ISO 1173 C 6.3
- with quick-action chuck
- adaptor with external hexagonal drive for powered use



| Code             | ○<br>mm | ○<br>" | ●     | "   | L<br>mm | Δ<br>g |   |
|------------------|---------|--------|-------|-----|---------|--------|---|
| <b>38 250002</b> | D 6.3   | 1/4    | E 6.3 | 1/4 | 62      | 27     | 1 |

inside ○/outside ● DIN 3126/ISO 1173

### 3115 Adaptor, manually operated

- for torque screwdrivers No 760 and No 775
- for manually operated sockets with recessed 6.3 (1/4") square drive DIN 3120/ISO 1174-1 Type C and D
- square drive with ball bearing
- Chrome Alloy Steel, gunmetal finish



| Code             | ■     | "   | ●     | "   | L<br>mm | d<br>mm | Δ<br>g |   |
|------------------|-------|-----|-------|-----|---------|---------|--------|---|
| <b>31 150001</b> | A 6.3 | 1/4 | E 6.3 | 1/4 | 50      | 8.9     | 16     | 5 |

outside ■ DIN 3120/ISO 1174-1 Type A (spring-loaded ball)  
outside ● DIN 3126/ISO 1173 Type E

### 3115/1 Adaptor, manually operated

- for manually operated sockets with recessed 6.3 (1/4") square drive
- DIN 3120/ISO 1174-1 Type C and D
- square drive with ball bearing
- Chrome Alloy Steel




| Code            | ■     | "   | ●     | "   | L<br>mm | △<br>g | ⊞ |
|-----------------|-------|-----|-------|-----|---------|--------|---|
| <b>31150002</b> | A 6.3 | 1/4 | C 6.3 | 1/4 | 25      | 10     | 5 |

outside ■ DIN 3120/ISO 1174-1 Type A (spring-loaded ball)  
outside ● DIN 3126/ISO 1173 Type E

### 3116/1-3316/1 Adaptor, machine operated

- DIN 7428/ISO 3317
- with outside hexagon
- for power operated IMPACT sockets DIN 3129/ISO 2725-2 with inside square DIN 3121/ISO 1174-2
- large collar diameter for better support of IMPACT sockets (3216/1, 3316/1)
- square drive with spring loaded locking pin
- Chrome Alloy Steel, gunmetal finish




| Code            | No            | ■      | "   | ●     | "   | L<br>mm | d<br>mm | △<br>g | ⊞ |
|-----------------|---------------|--------|-----|-------|-----|---------|---------|--------|---|
| <b>31160001</b> | <b>3116/1</b> | E 6.3  | 1/4 | E 6.3 | 1/4 | 50      | 8.9     | 16     | 5 |
| <b>32160001</b> | <b>3216/1</b> | E 10   | 3/8 | E 6.3 | 1/4 | 50      | 15.5    | 23     | 5 |
| <b>33160001</b> | <b>3316/1</b> | E 12.5 | 1/2 | E 6.3 | 1/4 | 50      | 18      | 34     | 5 |

outside ■ DIN 3121/ISO 1174-2 Type E (spring-loaded locking pin)  
outside ● DIN 3126/ISO 1173 Type E

### 3116/1QR-3316/1QR QuickRelease adaptor, machine operated

- with outside hexagon
- for power operated IMPACT sockets DIN 3129/ISO 2725-2 with inside square DIN 3121/ISO 1174-2
- large collar diameter for better support of IMPACT sockets
- Chrome Alloy Steel, gunmetal finish



| Code            | No              | ■      | "   | ●     | "   | L<br>mm | h<br>mm | △<br>g | ⊞ |
|-----------------|-----------------|--------|-----|-------|-----|---------|---------|--------|---|
| <b>31161001</b> | <b>3116/1QR</b> | E 6.3  | 1/4 | E 6.3 | 1/4 | 50      | 11.2    | 18     | 5 |
| <b>32161001</b> | <b>3216/1QR</b> | E 10   | 3/8 | E 6.3 | 1/4 | 50      | 14.6    | 26     | 5 |
| <b>33161001</b> | <b>3316/1QR</b> | E 12.5 | 1/2 | E 6.3 | 1/4 | 50      | 19.2    | 46     | 5 |

outside ● DIN 3126/ISO 1173 Type E

### 412/442/443/543 Bit holder

- square drive socket
  - for hand use only
  - for bit-screwdriver bits with outside hexagon 1/4" or 5/16"
  - DIN3126/ISO1173 C6.3 or C8
  - Chrome Alloy Steel, chrome plated
  - internal hexdrive with a collar-thrust spring (registered design).
- Bits are easy to insert, lock securely in position and can be removed just as easily; even hexbits with a wide groove (Type E, DIN3126/ISO1173)



| code            | No         | ○     | "    | ○      | "   | L<br>mm | d<br>mm | △<br>g | ⊞ |
|-----------------|------------|-------|------|--------|-----|---------|---------|--------|---|
| <b>11180010</b> | <b>412</b> | D 6.3 | 1/4  | C 6.3  | 1/4 | 25      | 11.6    | 14     | 5 |
| <b>12180026</b> | <b>442</b> | D 6.3 | 1/4  | C 10   | 3/8 | 32      | 16.5    | 30     | 5 |
| <b>12180030</b> | <b>443</b> | D 8   | 5/16 | C 10   | 3/8 | 32      | 16.5    | 39     | 5 |
| <b>13180010</b> | <b>543</b> | D 8   | 5/16 | C 12.5 | 1/2 | 38      | 22      | 65     | 5 |

inside ○ DIN 3126/ISO 1173  
inside ○ DIN 3120/ISO 1174-1

### 412-1 Bit holder

HPQ


- socket, hexagon 1/4" inside hexagon
- DIN 3126/ISO 1173 D 6.3
- outer size of handle, octagon 10 mm for use in tools with 10 mm internal hex drive or internal double hexagon (e.g. "FLEXI" double-ended flexi-joint spanners, T-handle universal joint spanners, box spanners, ratchet ring spanners etc.)
- internal hex drive with a collar-thrust spring
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)
- HPQ® high performance steel



| code            | mm | L<br>mm | d<br>mm | △<br>g | ⊞ |
|-----------------|----|---------|---------|--------|---|
| <b>11180020</b> | 10 | 20      | 11.6    | 11     | 5 |

### 736 Bit holder insert tools

- internal hex drive with a collar-thrust spring
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)



| Code            | size        | ○<br>mm | ○<br>" | mm   | b<br>mm | h<br>mm | S<br>mm | △<br>g |
|-----------------|-------------|---------|--------|------|---------|---------|---------|--------|
| <b>58261010</b> | <b>10</b>   | D 8     | 5/16   | 9x12 | 16      | 12.5    | 17.5    | 47     |
| <b>58262610</b> | <b>10-1</b> | D 6.3   | 1/4    | 9x12 | 14      | 10      | 17.5    | 45     |


inside ○ DIN 3126/ISO 1173

## Bit screwdrivers

- with outside hexagon 1/4"
- DIN 3126/ISO 1173, shape E 6.3
- for use in power drivers

### 1242-1250 Bit screwdrivers

- DIN 3127/ISO 2351
- for slotted screws



| Code     | No   | a x b<br>mm | Hex   | "   | L<br>mm | Weight<br>g | Box |
|----------|------|-------------|-------|-----|---------|-------------|-----|
| 08300635 | 1242 | 0.6 x 3.5   | E 6.3 | 1/4 | 50      | 8           | 10  |
| 08300840 | 1244 | 0.8 x 4.0   | E 6.3 | 1/4 | 50      | 9           | 10  |
| 08301055 | 1246 | 1.0 x 5.5   | E 6.3 | 1/4 | 50      | 10          | 10  |
| 08301265 | 1248 | 1.2 x 6.5   | E 6.3 | 1/4 | 50      | 11          | 10  |
| 08301680 | 1250 | 1.6 x 8.0   | E 6.3 | 1/4 | 50      | 14          | 10  |

outside • DIN 3126/ISO 1173

### 1260-1262 Bit screwdrivers

- DIN 3128
- for Phillips screws



| Code     | No   | PH<br>size | Hex   | "   | L<br>mm | Weight<br>g | Box |
|----------|------|------------|-------|-----|---------|-------------|-----|
| 08310001 | 1260 | 1          | E 6.3 | 1/4 | 50      | 10          | 10  |
| 08310002 | 1261 | 2          | E 6.3 | 1/4 | 50      | 11          | 10  |
| 08310003 | 1262 | 3          | E 6.3 | 1/4 | 50      | 11          | 10  |

outside • DIN 3126/ISO 1173

### 1270-1272 Bit screwdrivers

- for POZIDRIV/SUPADRIV® screws



| Code     | No   | PZ<br>size | Hex   | "   | L<br>mm | Weight<br>g | Box |
|----------|------|------------|-------|-----|---------|-------------|-----|
| 08320001 | 1270 | 1          | E 6.3 | 1/4 | 50      | 10          | 10  |
| 08320002 | 1271 | 2          | E 6.3 | 1/4 | 50      | 11          | 10  |
| 08320003 | 1272 | 3          | E 6.3 | 1/4 | 50      | 11          | 10  |

outside • DIN 3126/ISO 1173

### 1280-1284 Bit screwdrivers

- DIN 7426/ISO 3109
- for socket head screws



| Code     | No   | mm | Hex   | "   | L<br>mm | Weight<br>g | Box |
|----------|------|----|-------|-----|---------|-------------|-----|
| 08330003 | 1280 | 3  | E 6.3 | 1/4 | 50      | 9           | 10  |
| 08330004 | 1281 | 4  | E 6.3 | 1/4 | 50      | 10          | 10  |
| 08330005 | 1282 | 5  | E 6.3 | 1/4 | 50      | 12          | 10  |
| 08330006 | 1283 | 6  | E 6.3 | 1/4 | 50      | 13          | 10  |
| 08330008 | 1284 | 8  | E 6.3 | 1/4 | 50      | 18          | 10  |

outside • DIN 3126/ISO 1173

### 1290-1296 Bit screwdrivers

- for inside TORX® screws



| Code     | No   | size | Hex   | "   | L<br>mm | Weight<br>g | Box |
|----------|------|------|-------|-----|---------|-------------|-----|
| 08340010 | 1290 | T 10 | E 6.3 | 1/4 | 70      | 14          | 10  |
| 08340015 | 1291 | T 15 | E 6.3 | 1/4 | 70      | 14          | 10  |
| 08340020 | 1292 | T 20 | E 6.3 | 1/4 | 70      | 14          | 10  |
| 08340025 | 1293 | T 25 | E 6.3 | 1/4 | 70      | 15          | 10  |
| 08340027 | 1294 | T 27 | E 6.3 | 1/4 | 70      | 16          | 10  |
| 08340030 | 1295 | T 30 | E 6.3 | 1/4 | 70      | 16          | 10  |
| 08340040 | 1296 | T 40 | E 6.3 | 1/4 | 70      | 18          | 10  |

outside • DIN 3126/ISO 1173

### 1441 TN-1446 TN Torsion bit screwdrivers

- for inside TORX® screws
- specifically developed for use with professional battery-powered impact screwdrivers
- longer service lifetimes thanks to specially designed torsional shape, flexible material and high-grade hardening
- controlled machine handling close to the screw thanks to very compact construction




| Code     | No         | size | Hex   | "   | L<br>mm | Weight<br>g | Box |
|----------|------------|------|-------|-----|---------|-------------|-----|
| 08161115 | 1441 TN 15 | T 15 | E 6.3 | 1/4 | 38      | 4           | 5   |
| 08161120 | 1442 TN 20 | T 20 | E 6.3 | 1/4 | 38      | 5           | 5   |
| 08161125 | 1443 TN 25 | T 25 | E 6.3 | 1/4 | 38      | 6           | 5   |
| 08161130 | 1445 TN 30 | T 30 | E 6.3 | 1/4 | 38      | 7           | 5   |
| 08161140 | 1446 TN 40 | T 40 | E 6.3 | 1/4 | 38      | 8           | 5   |

outside • DIN 3126/ISO 1173

### 2801 Sockets

- with hexagon inserts for power drivers
- hexagon fitted with permanent magnet
- Chrome Alloy Steel, clear lacquered



| Code     | mm | Hex   | "   | d<br>mm | L<br>mm | Weight<br>g | Box |
|----------|----|-------|-----|---------|---------|-------------|-----|
| 28011007 | 7  | E 6.3 | 1/4 | 12      | 50      | 23          | 5   |
| 28011008 | 8  | E 6.3 | 1/4 | 13      | 50      | 26          | 5   |
| 28011010 | 10 | E 6.3 | 1/4 | 15.5    | 50      | 31          | 5   |
| 28011013 | 13 | E 6.3 | 1/4 | 18.7    | 50      | 44          | 5   |

### 13006 Special socket

- for use on plugs in electronic rack Airbus A320-A340



| Code     | Hex   | "   | Ø<br>mm | L<br>mm | Weight<br>g | Box |
|----------|-------|-----|---------|---------|-------------|-----|
| 08230001 | E 6.3 | 1/4 | 11      | 50      | 32          | 5   |

outside • DIN 3126/ISO 1173

## 4060 IMPACT driver set

- for screw sizes M5-M10
  - in sturdy, stackable ABS plastic case
- Content 1 each:
- IMPACT driver No 4030
  - adaptors No 4035; No 4036
  - ⊖ bit screwdrivers for slotted screws No 4040-4044
  - ⊕ bit screwdrivers for Phillips-screws No 4050-4052
  - bit screwdrivers for hex. socket head screws No 4055-4058



| Code              | g    |   |
|-------------------|------|---|
| <b>96 32 3001</b> | 1264 | 1 |

## 4030 IMPACT driver

- with inside hexagon for bit screwdriver inserts No 4040-4058
- suitable for screws M5-M10
- torque 120 N·m



| Code              | "   | L mm | g   |   |
|-------------------|-----|------|-----|---|
| <b>32 20 0005</b> | 3/8 | 138  | 604 | 1 |

## 4035/4036 Adaptors

- with outside hexagon
- for IMPACT screwdriver No 4030



| Code              | No          | "   | L mm | g  |   |
|-------------------|-------------|-----|------|----|---|
| <b>32 21 0001</b> | <b>4035</b> | 3/8 | 38   | 34 | 1 |
| <b>33 21 0001</b> | <b>4036</b> | 3/8 | 38   | 43 | 1 |

## 4040-4044 ⊖ Bit screwdrivers

- for slotted screws
- for IMPACT driver No 4030



| Code               | No          | a x b mm | "   | L mm | g  |    |
|--------------------|-------------|----------|-----|------|----|----|
| <b>08 40 00 10</b> | <b>4040</b> | 1.0 x 7  | 3/8 | 40   | 17 | 10 |
| <b>08 40 00 14</b> | <b>4041</b> | 1.4 x 9  | 3/8 | 40   | 20 | 10 |
| <b>08 40 00 16</b> | <b>4042</b> | 1.6 x 10 | 3/8 | 40   | 21 | 10 |
| <b>08 40 00 20</b> | <b>4043</b> | 2.0 x 12 | 3/8 | 40   | 20 | 10 |
| <b>08 40 00 15</b> | <b>4044</b> | 1.5 x 13 | 3/8 | 40   | 24 | 10 |

## 4050-4052 ⊕ Bit screwdrivers

- for Phillips screws (Phillips-Recess® DIN 5260)
- for IMPACT driver No 4030



| code               | No          | PH size | "   | L mm | g  |    |
|--------------------|-------------|---------|-----|------|----|----|
| <b>08 41 00 02</b> | <b>4050</b> | 2       | 3/8 | 35   | 17 | 10 |
| <b>08 41 00 03</b> | <b>4051</b> | 3       | 3/8 | 35   | 17 | 10 |
| <b>08 41 00 04</b> | <b>4052</b> | 4       | 3/8 | 35   | 17 | 10 |

## 4055-4058 ● Bit screwdrivers

- for socket head screws
- for IMPACT driver No 4030



| Code               | No          | mm | "   | L mm | g  |    |
|--------------------|-------------|----|-----|------|----|----|
| <b>08 42 00 05</b> | <b>4055</b> | 5  | 3/8 | 35   | 16 | 10 |
| <b>08 42 00 06</b> | <b>4056</b> | 6  | 3/8 | 35   | 16 | 10 |
| <b>08 42 00 08</b> | <b>4057</b> | 8  | 3/8 | 35   | 19 | 10 |
| <b>08 42 00 10</b> | <b>4058</b> | 10 | 3/8 | 35   | 23 | 10 |