

DETAILS

Product Number	FN15387_RONDA-WW
Family	Ronda
Type	Assembly
Color	white
Diameter	69,9 mm
Height	14,6 mm
Style	round
Optic Material	PMMA
Holder Material	
Fastening	
Status	production ready
ROHS Compliant	Yes
Date Updated	8/06/2017



OPTICAL PROPERTIES

LED	Viewing Angle	Light Beam	Efficiency	cd/lm	Connector
V13 Gen7	64 deg	Very Wide	82 %	0.680	TE: 2213254-2 + OPTIC CLIP Z50 TYPE1 2213194-1
V13 Gen7	sim: 59	Very Wide	sim: 89 %	sim: 0.800	IDEAL: 50-2103CT + 50-2100AN
V10 Gen6	NULL deg	Very Wide	sim: 88 %	-	LEDiL: LEDiL
VERO13	66 deg	Very Wide	88 %	0.710	LEDiL: LEDiL
V10 Gen7	47 deg	Very Wide	-	sim: 0.000	Bender Wirth: 434 Typ L1
V13 Gen7	sim: 60	Very Wide	sim: 88 %	sim: 0.851	Bender Wirth: 477 Typ L1
CLL02x/CLU02x (LES10)	NULL deg	Very Wide	sim: 88 %	-	Bender Wirth: 434 Typ L1
CLU700/701	NULL deg	Very Wide	sim: 89 %	-	Bender Wirth: 434 Typ L1
CLU710/711	NULL deg	Very Wide	sim: 88 %	-	Bender Wirth: 470 Typ L1
CXA/B 1816 & CXA/B 1820 & CXA 1850 sim: 57		Very Wide	sim: 85 %	-	TE: 2213401-2 + OPTIC CLIP Z50 TYPE1 2213194-1
CXA/B 15xx	NULL deg	Very Wide	sim: 89 %	-	LEDiL: LEDiL
CXA/B 1816 & CXA/B 1820 & CXA 1850 NULL deg		Very Wide	sim: 89 %	-	LEDiL: LEDiL
CXA/B 1830	NULL deg	Very Wide	sim: 87 %	-	LEDiL: LEDiL
CXA/B 13xx	NULL deg	Very Wide	sim: 89 %	-	Bender Wirth: 448 Typ L1
CXA/B 15xx	NULL deg	Very Wide	sim: 89 %	-	Bender Wirth: 441 Typ L1
CXA/B 1816 & CXA/B 1820 & CXA 1850 NULL deg		Very Wide	sim: 89 %	-	Bender Wirth: 437 Typ L1
LUXEON CoB 1202/1203	sim: 56	Very Wide	sim: 87 %	-	TE: 2213382-2 + OPTIC CLIP Z50 TYPE1 2213194-1
LUXEON CoB 1202s	NULL deg	Very Wide	sim: 89 %	-	Bender Wirth: 452 Typ L1
COB L-Type (LES 9)	sim: 56	Very Wide	sim: 87 %	-	TE: 2213382-2 + OPTIC CLIP Z50 TYPE1 2213194-1
NSCXL036A	sim: 56	Very Wide	sim: 88 %	-	TE: 2213382-2 + OPTIC CLIP Z50 TYPE1 2213194-1
COB J-Type	60 deg	Very Wide	81 %	0.640	IDEAL: 50-2103NC + 50-2100AN
Soleriq S13	NULL deg	Very Wide	sim: 84 %	-	LEDiL: LEDiL
Duris S10	NULL deg	Very Wide	sim: 89 %	-	LEDiL: LEDiL
Fortimo SLM G5 LES 15 Standard	66 deg	Very Wide	83 %	0.610	TE: OPTIC CLIP Z50 TYPE1 2213194-1
LC040C	60 deg	Very Wide	86 %	0.830	TE: 2213382-2 + OPTIC CLIP Z50 TYPE1 2213194-1



PRODUCT DATASHEET

Ronda series

last update 8/6/2017

OPTICAL PROPERTIES

LED	Viewing Angle	Light Beam	Effi- ciency	cd/lm	Connector
AC Zhaga COB	67 deg	Very Wide	84 %	0.610	Optosource: SEHSMJD-A
MJT COB LES 14.5	69 deg	Very Wide	80 %	0.600	TE: 2213254-2 + OPTIC CLIP Z50 TYPE1 2213194-1
Mini Zenigata (GW6BM)	NULL deg	Very Wide	sim: 88 %	-	Bender Wirth: 452 Typ L1
SLE G6 LES15	sim: 62	Very Wide	sim: 82 %	sim: 0.740	TE: 2213254-2 + OPTIC CLIP Z50 TYPE1 2213194-1

4

3

2


1

4

3


2

1




Front plate examples

D=49.9





Optic

D=69.9mm



Ledil-clamp / TE / Bender-wirth / other twist and lock socket types (holder A)






BJB and Stucchi 50mm (holder B)




LES size up to ~14mm, see compatibility www.ledil.com

See more details on page 2 and 3



Examples

Horizontal fix: M3 Nut + bolt




Rotation fix


Vertical fix: M3 Screw / Twist and lock / Snap

Tolerances if not otherwise shown According to DIN ISO 2768-1 Linear measures: up to 30mm class M, otherwise class C According to DIN ISO 2768-2 Form and position: class L		LEDiL Ledil Oy Salorankatu 10 FIN 24240 SALO Finland	
THIRD ANGLE PROJECTION: 		DRAWING TITLE RONDA-family	
This drawing is the property of LEDiL Oy. It may not be reproduced, copied or communicated without a written agreement with LEDiL Oy.		SIZE A3	PART NUMBER -
		SCALE 1:1	WEIGHT - SHEET 1/3


Bottom view




Front view




Top view



Front panel location suggestion when seamless look needed




Detail A




Isometric view

* Ensure from 3d according specific optic version


Tolerances if not otherwise shown According to DIN ISO 2768-1 Linear measures: up to 30mm class M, otherwise class C According to DIN ISO 2768-2 Form and position: class L		LEDiL Ledil Oy Salorankatu 10 FIN 24240 SALO Finland	
THIRD ANGLE PROJECTION: 		DRAWING TITLE RONDA-family	
This drawing is the property of LEDiL Oy. It may not be reproduced, copied or communicated without a written agreement with LEDiL Oy.		SIZE A3	PART NUMBER -
		SCALE 1:1	WEIGHT - SHEET 2/3

OPTIC/HOLDER ASSEMBLY


1. Place pin on the side of the lens into relative hole on the holder.



2. Press the lens under clips on the holder, ensuring both clips are fixed.



TYPICAL CONNECTOR ASSEMBLY (including solderless BENDER WIRTH as example)




Bender&Wirth model 4xx Typ L1

Align clamp positioning pin with holes in the connector.

Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures:
up to 30mm class M, otherwise class C
According to DIN ISO 2768-2
Form and position: class L

THIRD ANGLE PROJECTION:



This drawing is the property
of LEDiL Oy. It may not be
reproduced, copied or
communicated without a written
agreement with LEDiL Oy.

LEDiL Ledil Oy
Salorankatu 10
FIN 24240 SALO
Finland

DRAWING TITLE

RONDA-family

SIZE PART NUMBER

A3

-


SCALE 1:1 WEIGHT

-


SHEET 3/3

Luminaire: LEDiL Oy FN15387_RONDA-WW_(V13_Gen7)+TE


Lamps: 1 x Bridgelux_V13_Gen7_(BXRE-30E2000-B_+TE_2213254-2+TE_2213194-1)_1295.55lm@250mA_P=8.30985W_I=0.25A




Luminaire: LEDiL Oy FCN15315_RONDA-WW_(VERO13)
Lamps: 1 x Bridgelux_VERO13_(BXRC-30E2000-C-Z3)_+C13658_CLAMP-VERO13-18_956.274lm@250mA_CCT=3000K_P=7.59867W_I=0.25A




Luminaire: LEDiL Oy FCN15315_RONDA-WWW_(V10_Gen7)
Lamps: 1 x Bridgelux_V10_Gen7_(BXRE-30G2000-B)_953.189lm@250mA_P=8.52368W_I=0.25A




Luminaire: LEDiL Oy FN15387_RONDA-WW_(NFDLJ130B+IDEAL)
Lamps: 1 x Nichia_NFDLJ130B_+50-2103NC_+50-2100AN_1422.52lm@250mA_CCT=4000K_P=8.91686W_I=0.25A




Luminaire: Ledil FN15387_RONDA-WW_(SLM_G5_LES_15_+TE_2213194-1)
Lamps: 1 x Philips_SLM_G5_LES_15_+TE_2213194-1_1275.04lm@250mA_P=8.2035W_I=0.25A




Luminaire: Ledil FN15387_RONDA-WW_(LC040C+TE)
Lamps: 1 x Samsung_LC040C+_2213382-2+_2213194-1_1194.16lm@250mA_CCT=4000K_P=8.137W




Luminaire: Ledil FN15387_RONDA-WW_(SEOUL_AC_Zhaga_COB)
Lamps: 1 x SEOUL_AC_Zhaga_COB



Luminaire: Ledil FN15387_RONDA-WW_(MJT_30W_Les14,5)
Lamps: 1 x Seoul_MJT_30W_Les14,5mm_(SAWx1566A)_1328.6lm@250mA_P=8.24025W_I=0.25A




Luminaire: Ledil Oy FN15387_RONDA-WW_(SLE_G6_LES15)_(2213254-2+_2213194-1)_SIMULATED
Lamps: 1 x Tridonic SLE G6 LES15 + Tyco Electronics 2213254-2 + TE 2213194-1 Optic clip




Luminaire: LEDiL Oy FN15387_RONDA-WW_(V13_Gen7)+TE

Lamps: 1 x Bridgelux_V13_Gen7_(BXRE-30E2000-B_+TE_2213254-2+TE_2213194-1)_1295.55lm@250mA_P=8.30985W_I=0.25A




Luminaire: LEDiL Oy FCN15315_RONDA-WW_(VERO13)
Lamps: 1 x Bridgelux_VERO13_(BXRC-30E2000-C-Z3)_+C13658_CLAMP-VERO13-18_956.274lm@250mA_CCT=3000K_P=7.59867W_I=0.25A




Luminaire: LEDiL Oy FCN15315_RONDA-WW_(V10_Gen7)

Lamps: 1 x Bridgelux_V10_Gen7_(BXRE-30G2000-B)_953.189lm@250mA_P=8.52368W_I=0.25A




Luminaire: LEDiL Oy FN15387_RONDA-WW_(NFDLJ130B+IDEAL)
Lamps: 1 x Nichia_NFDLJ130B_+50-2103NC_+50-2100AN_1422.52lm@250mA_CCT=4000K_P=8.91686W_I=0.25A



Luminaire: Ledil FN15387_RONDA-WWW_(SLM_G5_LES_15_+TE_2213194-1)

Lamps: 1 x Philips_SLM_G5_LES_15_+TE_2213194-1_1275.04lm@250mA_P=8.2035W_I=0.25A



cd/klm


$\eta = 83\%$

— C0 - C180

— C90 - C270

Luminaire: Ledil FN15387_RONDA-WW_(LC040C+TE)

Lamps: 1 x Samsung_LC040C+_2213382-2+_2213194-1_1194.16lm@250mA_CCT=4000K_P=8.137W




cd/klm

— C0 - C180

— C90 - C270


$\eta = 86\%$

Luminaire: Ledil FN15387_RONDA-WW_(SEOUL_AC_Zhaga_COB)
Lamps: 1 x SEOUL_AC_Zhaga_COB




Luminaire: Ledil FN15387_RONDA-WW_(MJT_30W_Les14,5)

Lamps: 1 x Seoul_MJT_30W_Les14,5mm_(SAWx1566A)_1328.6lm@250mA_P=8.24025W_I=0.25A



Luminaire: Ledil Oy FN15387_RONDA-WW_(SLE_G6_LES15)_(2213254-2_+ 2213194-1)_SIMULATED
Lamps: 1 x Tridonic SLE G6 LES15 + Tyco Electronics 2213254-2 + TE 2213194-1 Optic clip



NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

GENERAL INFORMATION

- Product series especially designed & optimized for series of LEDs.
- Special care taken to make light distribution as uniform as possible.

Note! Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.