



RVT43HLTNWC00

IPS RGB 4.3" LCD TFT Datasheet

Rev.1.0

2020-08-05

ITEM	CONTENTS	UNIT
LCD Type	TFT/Transmissive/Normally black/IPS	/
Size	4.3	Inch
Viewing Direction	Free	/
Outside Dimensions (W × H × D)	120.38 x 79.20 x 5.10	mm ³
Active Area (W × H)	95.04 × 53.86	mm ²
Pixel Pitch (W × H)	0.198 × 0.198	mm ²
Resolution	480 (RGB) × 272	/
Brightness	800	cd/m ²
LCD Interface Type	RGB	/
Color Depth	16.7 M	/
Pixel Arrangement	RGB Vertical Stripe	/
LCD Driver	SC7283	/
With/Without Touch	With Projected Capacitive Touch Panel	/
CTP Driver	ILI2132A	/
Touch Interface	USB/I2C/Optional UART	/
Weight	87	g

Note 1: RoHS compliant

Note 2: LCM weight tolerance: ± 5%.

REVISION RECORD

REVNO.	REVDATE	CONTENTS	REMARKS
1.0	2020-08-05	Initial Release	

CONTENTS

REVISION RECORD.....	2
1 MODULE CLASSIFICATION INFORMATION	3
2 UxTOUCH ASSEMBLY	4
3 MODULE DRAWING.....	5
4 ABSOLUTE MAXIMUM RATINGS.....	6
5 ELECTRICAL CHARACTERISTICS.....	6
6 BACKLIGHT DRIVING CONDITIONS	6
7 ELECTRO-OPTICAL CHARACTERISTICS	7
8 BLOCK DIAGRAM	9
9 INTERFACE DESCRIPTION	10
9.1 TFT assignment.....	10
9.2 Touch panel assignment.....	10
9.3 CON1 assignment	10
10 TIMING CHARACTERISTICS	11
10.1 Timing diagram and input setup timing setting	11
10.1.1 SYNC mode timing diagram.....	11
10.1.2 SYNC-DE mode timing diagram	12
10.1.3 DE mode timing diagram	13
10.2 Parallel 24-bit RGB input timing table	14
10.3 Power ON/OFF sequence	14
10.3.1 Power on sequence	14
10.3.2 Power off sequence.....	14
11 CAPACITIVE TOUCH SCREEN PANEL SPECIFICATIONS	15
11.1 Mechanical characteristics	15
11.2 Electrical characteristics	15
12 INSPECTION	16
12.1 Inspection condition.....	16
12.2 Inspection standard.....	17
13 RELIABILITY TEST.....	19
14 LEGAL INFORMATION.....	20

1 MODULE CLASSIFICATION INFORMATION

RV	T	43	H	L	T	N	W	C	00
1.	2.	3.	4.	5.	6.	7.	8.	9.	10.


1.	BRAND	RV – Riverdi
2.	PRODUCT TYPE	T – TFT Standard
3.	DISPLAY SIZE	43 – 4.3”
4.	MODEL SERIAL NO.	H – High Brightness, IPS
5.	RESOLUTION	L – 480 x 272 px
6.	INTERFACE	T– TFT LCD, RGB
7.	FRAME	N – No Frame
8.	BACKLIGHT TYPE	W – LED White
9.	TOUCH PANEL	C – With Capacitive Touch Panel
10.	VERSION	00 – (00-99)

2 UxTOUCH ASSEMBLY








UxTouch are LCD TFT displays with specially designed projected capacitive touch panels. UxTouch display can be mounted without any hole in the housing. Our standard UxTouch displays include double-sided adhesive tape (DST) to stick TFT easily to the housing. Basic series include 4.3", 5.0" and 7.0" display sizes.

UxTouch models with double-side adhesive tape (PN with endings 00, 01, 03, 04) can be mounted by connecting the glass to the housing. Riverdi recommends to use support brackets assembled to display's back. An additional support will stiffen the whole structure and minimize the influence of external factors such as vibration. Figure 1 below shows examples of using support elements.

Figure 1. Example of using support brackets



Revision:	Changes:	Date:
1.0	Initial Case	2020.07.16



TFT NOTES: 1. LCD TYPE: TRANSMISSIVE, NORMALLY BLACK, IPS 2. RESOLUTION: 480x272 3. VIEWING ANGLE: FREE 4. INTERFACE: RGB 5. LCD DRIVER: SC7283 6. LOGIC VOLTAGE: 3.3V 7. BACKLIGHT: 16PCS LED, V _F =25.6V(TYP), I _F =40mA(TYP)	TP NOTES: 1. TP STRUCTURE: G+G 2. CG THICKNESS:1.10mm 3. DRIVER IC: ILI2132A 4. INTERFACE: USB; I2C; OPTIONAL UART 5. OPERATING VOLTAGE: 3.3V(CTP I2C); 5.0V(CTP USB);	GENERAL NOTES: 1. MODULE SURFACE LUMINANCE: 800 cd/m^2 2. OPERATING TEMPERATURE: -20°C ~ 70°C 3. STORAGE TEMPERATURE: -30°C ~ 80°C 4. WITHOUT INDIVIDUAL TOLERANCE: DIM ACCORDING DIRECTLY TO TFT: ±0.2mm DIM ACCORDING DIRECTLY TO TP: ±0.3mm 5. RoHS COMPLIANT					
			PN: RVT43HLTNWC00				
			SN:				
			DRAWN: Mateusz Natywa		2020.07.16	1:2.00	
			CHECKED: P.Mudlaw		2020.07.16	[mm]	
			APPR:				
			ISO A3	P. 1 of 1			

4 ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	MIN	MAX	UNIT	NOTE
Operating Ambient temperature	T _{OP}	-20	70	°C	At 25±5°C
Storage Temperature	T _{ST}	-30	80	°C	
Operating Ambient Humidity	H _{OP}	10	-	% RH	
Storage Ambient Humidity	H _{ST}	10	-	% RH	
Power for Circuit Driving	V _{dd}	-0.3	4.6	V	
Power for Circuit Logic	V _t	-0.3	V _{dd} + 0.3	V	

Note. The following are maximum values. If exceeded it may cause operation or damage to the unit.

5 ELECTRICAL CHARACTERISTICS

PARAMETER		SYMBOL	MIN	TYP	MAX	UNIT
Power Supply for Analog Circuit		VDD	3.0	3.3	3.6	V
Logic Input Voltage	Low Voltage	VIL	0	-	0.3VDD	V
	High Voltage	VIH	0.7VDD	-	VDD	V
Logic Output Voltage	Low Voltage	VOL	0	-	0.2VDD	V
	High Voltage	VOH	0.8VDD	-	-	V
Power Consumption	Black Mode	Pb	-	20	25	mW
	Standby Mode	Pw	-	40	50	mW

6 BACKLIGHT DRIVING CONDITIONS

PARAMETER	SYMBOL	MIN	TYP	MAX	UNIT	NOTE
Backlight Driving Voltage	V _F	24.4	25.6	27.2	V	Note 1,2
Backlight Driving Current	I _F	-	40	-	mA	
Backlight Power Consumption	W _{BL}	-	1024	-	mW	
Backlight Life Time	-	-	50,000	-	Hrs	Note 3

Note 1. Unless specified, the ambient temperature Ta=25°C.

Note 2. The recommended operating conditions refer to a range in which operation of this product is guaranteed. Should this range is exceeded, the operation cannot be guaranteed even if the values may be without the absolute maximum ratings.

Note 3. If LED is driven by high current, high ambient temperature & humidity condition. The life time of LED will be reduced. Operating life means brightness goes down to 50% initial brightness. Typical operating life time is estimated data.

7 ELECTRO-OPTICAL CHARACTERISTICS

Optical characteristics are determined after the unit has been 'ON' and stable for approximately 30 minutes in a dark environment at 25 °C. The values specified are at an approximate distance 500mm from the LCD surface at a viewing angle of Φ and θ equal to 0°.

ITEM	SYMBOL	CONDITION	MIN	TYP	MAX	UNIT	REMARK	NOTE
Response Time	Tr+Tf	$\theta=0^\circ$ $\phi=0^\circ$ Ta=25 °C	-	30	40	ms	FIG 2.	4
Contrast Ratio	Cr		640	800	-	---	FIG 3.	1
Luminance Uniformity	δ WHITE		-	75	-	%	FIG 3.	3
Surface Luminance	Lv		-	800	-	cd/m ²	FIG 3.	2
Viewing Angle Range	θ	$\phi = 90^\circ$	70	80	-	deg	FIG 4.	6
		$\phi = 270^\circ$	70	80	-	deg	FIG 4.	
		$\phi = 0^\circ$	70	80	-	deg	FIG 4.	
		$\phi = 180^\circ$	70	80	-	deg	FIG 4.	
CIE (x, y) Chromaticity	Red	x	0.579	0.619	0.659	FIG 3.		5
		y	0.290	0.330	0.370			
	Green	x	0.346	0.386	0.426			
		y	0.539	0.579	0.619			
	Blue	x	0.070	0.110	0.150			
		y	0.091	0.131	0.171			
	White	x	0.280	0.320	0.360			
		y	0.305	0.345	0.384			

Note 1. Contrast Ratio(CR) is defined mathematically as below, for more information see Figure 12.

$$\text{Contrast Ratio} = \frac{\text{Average Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}}{\text{Average Surface Luminance with all black pixels (P1, P2, P3, P4, P5)}}$$

Note 2. Surface luminance is the LCD surface from the surface with all pixels displaying white. For more information see Figure 23.

$$Lv = \text{Average Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}$$

Note 3. The uniformity in surface luminance δ WHITE is determined by measuring luminance at each test position 1 through 5, and then dividing the maximum luminance of 5 points luminance by minimum luminance of 5 points luminance. For more information see Figure 23.

$$\delta \text{ WHITE} = \frac{\text{Minimum Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}}{\text{Maximum Surface Luminance with all white pixels (P1, P2, P3, P4, P5)}}$$

Note 4. Response time is the time required for the display to transition from white to black (Rise Time, Tr) and from black to white (Decay Time, Tf). For additional information see Figure 1. The test equipment is Autronic-Melchers's ConoScope series.

Note 5. CIE (x, y) chromaticity, the x, y value is determined by measuring luminance at each test position 1 through 5, and then make average value.

Note 6. Viewing angle is the angle at which the contrast ratio is greater than 2. For TFT module the contrast ratio is greater than 10. The angles are determined for the horizontal or x axis and the vertical or y axis with respect to the z axis which is normal to LCD surface. For more information see Figure 4.

Note 7. For viewing angle and response time testing, the testing data is based on Autronic-Melchers's ConoScope series. Instruments for Contrast Ratio, Surface Luminance, Luminance Uniformity, CIE the test data is based on TOPCON's BM-5 photo detector.

Figure 2. The definition of response time




Figure 3. Measuring method for Contrast ratio, surface luminance, Luminance uniformity, CIE (x, y) chromaticity

A : 5 mm
B : 5 mm
H, V : Active Area
Light spot size $\varnothing=5\text{mm}$, 500mm distance from the LCD surface to detector lens
measurement instrument is TOPCON's luminance meter BM-5






Figure 4. The definition of viewing angle



8 BLOCK DIAGRAM



9 INTERFACE DESCRIPTION

9.1 TFT assignment

PIN NO.	SYMBOL	DESCRIPTION
1	VLED-	Backlight Power Input PIN Cathode
2	VLED+	Backlight Power Input PIN Anode
3	GND	Ground
4	VDD	Power Supply Voltage
5-12	R0-R7	Red Data
13-20	G0-G7	Green Data
21-28	B0-B7	Blue Data
29	GND	Ground
30	DCLK	Data Clock Signal
31	DISP	Standby Mode DISP="1", Normal Operation DISP="0", Standby Mode.
32	HSYNC	Horizontal Synchronized Signal
33	VSYNC	Vertical Synchronized Signal
34	DE	Data Input Enable
35	NC	Not Connect
36	GND	Ground
37	NC/XR	No Connection If without TP
38	NC/YD	No Connection If without TP
39	NC/XL	No Connection If without TP
40	NC/YU	No Connection If without TP

9.2 Touch panel assignment

PIN NO.	SYMBOL	DESCRIPTION
1	USB_GND	USB_Ground
2	USB_VDD	USB_Power for CTP, DC 5.0 V
3	USB_D-	USB_Data Signal -
4	USB_D+	USB_Data Signal +
5	I2C_GND	I2C_Ground
6	I2C_VDD	I2C_Power For CTP, DC 3.3 V
7	I2C_RST	I2C_Reset Pin
8	I2C_SCL	I2C_Clock Input
9	I2C_INT	I2C_Interrupt Signal from CTP
10	I2C_SDA/TXD	I2C_Data Signal


9.3 CON1 assignment

PIN NO.	SYMBOL	DESCRIPTION
1	USB_VDD	USB_Power for CTP, DC 5.0V
2	USB_D-	USB_Data Signal -
3	USB_D+	USB_Data Signal +
4	USB_GND	USB_Ground


10 TIMING CHARACTERISTICS

10.1 Timing diagram and input setup timing setting


10.1.1 SYNC mode timing diagram



10.1.2 SYNC-DE mode timing diagram



10.1.3 DE mode timing diagram



RGB MODE SELECTION	DCLK	HSYNC	VSYNC	DE
SYNC-DE Mode	Input	Input	Input	Input
SYNC Mode	Input	Input	Input	GND
DE Mode	Input	GND	GND	Input

Note. "Input" means these signals are driven by host side.

10.2 Parallel 24-bit RGB input timing table


Parallel 24-bit RGB input Timing (PVDD=VDD=VDDI=3.3V, AGND=0V, Ta=25 °C)

PARAMETER	SYMBOL	MIN	TYP	MAX	UNIT	NOTE
DCLK Frequency	Fclk	8	9	12	MHz	
DCLK Period	Tclk	83	111	125	ns	
HSYNC	Period Time	Th	485	531	598	DCLK
	Display Period	Thdisp	480			DCLK
	Back Porch	Thbp	3	43	43	DCLK
	Front Porch	Thfp	2	8	75	DCLK
	Pluse Width	Thw	2	4	43	DCLK
VSYNC	Period Time	Tv	276	292	321	HSYNC
	Display Period	Tvdisp	272			HSYNC
	Back Porch	Tvbp	2	12	12	HSYNC
	Front Porch	Tvfp	2	8	37	HSYNC
	Pluse Width	Tvw	2	4	12	HSYNC

Note. It's necessary to keep Tvbp=12 and Thbp=43 in sync mode. DE mode is unnecessary to keep it.


10.3 Power ON/OFF sequence

10.3.1 Power on sequence



SYMBOL	DESCRIPTION	MIN. TIME	UNIT
T0	System power stability to GRB RESET signal	0	ms
T1	GRB RESET="High " to DISP="High "	10	ms
T2	Display Signal output to Backlight Power on	250	ms

10.3.2 Power off sequence



SYMBOL	DESCRIPTION	MIN. TIME	UNIT
T0	Backlight Power off to DISP="Low "	5	ms
T1	DISP = "Low " to IC internal voltage discharge complete	80	ms

11 CAPACITIVE TOUCH SCREEN PANEL SPECIFICATIONS

11.1 Mechanical characteristics

DESCRIPTION	SPECIFICATION	REMARK
Touch Panel Size	4.3 inch	UxTouch
Outline Dimension of CTP	120.38 mm x 79.20 mm	UxTouch
Product Thickness	2.15 mm	UxTouch
Glass Thickness	1.1 mm	UxTouch
CTP View Area	96.54 mm x 55.36 mm	UxTouch
Sensor Active Area	98.00 mm x 56.50 mm	UxTouch
Structure type	Glass + Glass	UxTouch
Surface Hardness	6H	UxTouch

11.2 Electrical characteristics

DESCRIPTION		SPECIFICATION
Operating Voltage		DC 5.0 V (USB)
		DC 3.3 V (I ² C)
Power Consumption (IDD)	Active Mode	90 mA
	Sleep Mode	10 mA
Interface		USB / I ² C/Optional UART
Linearity		+/-1.5mm
Controller		ILI2132A
I2C address		0X82
Resolution		480 x 272

12 INSPECTION

Standard acceptance/rejection criteria for TFT module.

12.1 Inspection condition

Ambient conditions:


- Temperature: $25 \pm 2^{\circ}\text{C}$
- Humidity: $(60 \pm 10)\% \text{RH}$
- Illumination: Single fluorescent lamp non-directive (300 to 700 lux)

Viewing distance:



$35 \pm 5 \text{cm}$ between inspector bare eye and LCD.

Viewing Angle:

U/D: $45^{\circ}/45^{\circ}$, L/R $45^{\circ}/45^{\circ}$



12.2 Inspection standard

Item	Criterion																																	
Black spots, white spots, light leakage, Foreign Particle (round Type)	 $D = \frac{(x + y)}{2}$ *Spots density: 10 mm <table><tr><th colspan="2">3.5" ≤ Size ≤ 5"</th></tr><tr><th>Average Diameter</th><th>Qualified Qty</th></tr><tr><td>D ≤ 0.15 mm</td><td>Ignored</td></tr><tr><td>0.15 mm < D ≤ 0.30 mm</td><td>N≤3</td></tr><tr><td>0.3mm < D</td><td>Not allowed</td></tr></table> <table><tr><th colspan="2">Size =7"</th></tr><tr><th>Average Diameter</th><th>Qualified Qty</th></tr><tr><td>D ≤ 0.2 mm</td><td>Ignored</td></tr><tr><td>0.2 mm < D ≤ 0.3 mm</td><td>N≤3</td></tr><tr><td>0.5mm < D</td><td>Not allowed</td></tr></table>	3.5" ≤ Size ≤ 5"		Average Diameter	Qualified Qty	D ≤ 0.15 mm	Ignored	0.15 mm < D ≤ 0.30 mm	N≤3	0.3mm < D	Not allowed	Size =7"		Average Diameter	Qualified Qty	D ≤ 0.2 mm	Ignored	0.2 mm < D ≤ 0.3 mm	N≤3	0.5mm < D	Not allowed													
3.5" ≤ Size ≤ 5"																																		
Average Diameter	Qualified Qty																																	
D ≤ 0.15 mm	Ignored																																	
0.15 mm < D ≤ 0.30 mm	N≤3																																	
0.3mm < D	Not allowed																																	
Size =7"																																		
Average Diameter	Qualified Qty																																	
D ≤ 0.2 mm	Ignored																																	
0.2 mm < D ≤ 0.3 mm	N≤3																																	
0.5mm < D	Not allowed																																	
LCD black spots, white spots, light leakage (line Type)	 *Spots density: 10 mm <table><tr><th colspan="3">3.5" ≤ Size ≤ 5"</th></tr><tr><th>Length/mm</th><th>Width/mm</th><th>Qualified Qty</th></tr><tr><td>-</td><td>W≤ 0.03</td><td>Ignored</td></tr><tr><td>L ≤ 3.0</td><td>0.03< W ≤ 0.05</td><td>2</td></tr><tr><td>L ≤ 3.0</td><td>0.05 < W ≤ 0.1</td><td>1</td></tr><tr><td>3.0 < L</td><td>0.1< W</td><td>Not allowed</td></tr></table> <table><tr><th colspan="3">Size =7"</th></tr><tr><th>Length</th><th>Width</th><th>Qualified Qty</th></tr><tr><td>-</td><td>W ≤ 0.05</td><td>Ignored</td></tr><tr><td>L ≤ 5.0</td><td>0.05< W ≤ 0.1</td><td>3</td></tr><tr><td>5.0 < L</td><td>0.10< W</td><td>Not allowed</td></tr></table>	3.5" ≤ Size ≤ 5"			Length/mm	Width/mm	Qualified Qty	-	W≤ 0.03	Ignored	L ≤ 3.0	0.03< W ≤ 0.05	2	L ≤ 3.0	0.05 < W ≤ 0.1	1	3.0 < L	0.1< W	Not allowed	Size =7"			Length	Width	Qualified Qty	-	W ≤ 0.05	Ignored	L ≤ 5.0	0.05< W ≤ 0.1	3	5.0 < L	0.10< W	Not allowed
3.5" ≤ Size ≤ 5"																																		
Length/mm	Width/mm	Qualified Qty																																
-	W≤ 0.03	Ignored																																
L ≤ 3.0	0.03< W ≤ 0.05	2																																
L ≤ 3.0	0.05 < W ≤ 0.1	1																																
3.0 < L	0.1< W	Not allowed																																
Size =7"																																		
Length	Width	Qualified Qty																																
-	W ≤ 0.05	Ignored																																
L ≤ 5.0	0.05< W ≤ 0.1	3																																
5.0 < L	0.10< W	Not allowed																																
Bright/Dark Dots	<table><tr><th colspan="2">3.5" ≤ Size ≤ 5"</th></tr><tr><th>item</th><th>Qualified Qty</th></tr><tr><td>Bright Dots</td><td>N≤1</td></tr><tr><td>Dark Dots</td><td>N≤2</td></tr><tr><td>Total Bright and Dark Dots</td><td>N≤3</td></tr></table> <table><tr><th colspan="2">Size =7"</th></tr><tr><th>item</th><th>Qualified Qty</th></tr><tr><td>Bright Dots</td><td>N≤2</td></tr><tr><td>Dark Dots</td><td>N≤3</td></tr><tr><td>Total Bright and Dark Dots</td><td>N≤4</td></tr></table>	3.5" ≤ Size ≤ 5"		item	Qualified Qty	Bright Dots	N≤1	Dark Dots	N≤2	Total Bright and Dark Dots	N≤3	Size =7"		item	Qualified Qty	Bright Dots	N≤2	Dark Dots	N≤3	Total Bright and Dark Dots	N≤4													
3.5" ≤ Size ≤ 5"																																		
item	Qualified Qty																																	
Bright Dots	N≤1																																	
Dark Dots	N≤2																																	
Total Bright and Dark Dots	N≤3																																	
Size =7"																																		
item	Qualified Qty																																	
Bright Dots	N≤2																																	
Dark Dots	N≤3																																	
Total Bright and Dark Dots	N≤4																																	

Item	Criterion																					
Clear spots	<table><tr><th colspan="3">Size < 5"</th></tr><tr><td colspan="2">Average Diameter</td><td>Qualified Qty</td></tr><tr><td colspan="2">D < 0.2 mm</td><td>Ignored</td></tr><tr><td colspan="2">0.2 mm < D < 0.3 mm</td><td>3</td></tr><tr><td colspan="2">0.3 mm < D < 0.5 mm</td><td>2</td></tr><tr><td colspan="2">0.5 mm < D</td><td>0</td></tr></table>	Size < 5"			Average Diameter		Qualified Qty	D < 0.2 mm		Ignored	0.2 mm < D < 0.3 mm		3	0.3 mm < D < 0.5 mm		2	0.5 mm < D		0			
	Size < 5"																					
	Average Diameter		Qualified Qty																			
	D < 0.2 mm		Ignored																			
	0.2 mm < D < 0.3 mm		3																			
	0.3 mm < D < 0.5 mm		2																			
	0.5 mm < D		0																			
	<table><tr><th colspan="3">Size >= 5"</th></tr><tr><td colspan="2">Average Diameter</td><td>Qualified Qty</td></tr><tr><td colspan="2">D<0.2 mm</td><td>Ignored</td></tr><tr><td colspan="2">0.2 mm < D < 0.3 mm</td><td>4</td></tr><tr><td colspan="2">0.3 mm < D < 0.5 mm</td><td>2</td></tr><tr><td colspan="2">0.5 mm < D</td><td>0</td></tr></table>	Size >= 5"			Average Diameter		Qualified Qty	D<0.2 mm		Ignored	0.2 mm < D < 0.3 mm		4	0.3 mm < D < 0.5 mm		2	0.5 mm < D		0			
	Size >= 5"																					
	Average Diameter		Qualified Qty																			
	D<0.2 mm		Ignored																			
	0.2 mm < D < 0.3 mm		4																			
	0.3 mm < D < 0.5 mm		2																			
	0.5 mm < D		0																			
*Spots density: 10 mm																						
Polarizer bubbles	<table><tr><th colspan="3">3.5" ≤ Size ≤ 5"</th></tr><tr><td colspan="2">Average Diameter</td><td>Qualified Qty</td></tr><tr><td colspan="2">D ≤ 0.2 mm</td><td>Ignored</td></tr><tr><td colspan="2">0.2 mm < D ≤ 0.3 mm</td><td>2</td></tr><tr><td colspan="2">0.3 mm < D ≤ 0.5mm</td><td>1</td></tr><tr><td colspan="2">0.5 mm < D</td><td>0</td></tr><tr><td colspan="2">Total Q'ty</td><td>3</td></tr></table>	3.5" ≤ Size ≤ 5"			Average Diameter		Qualified Qty	D ≤ 0.2 mm		Ignored	0.2 mm < D ≤ 0.3 mm		2	0.3 mm < D ≤ 0.5mm		1	0.5 mm < D		0	Total Q'ty		3
	3.5" ≤ Size ≤ 5"																					
	Average Diameter		Qualified Qty																			
	D ≤ 0.2 mm		Ignored																			
	0.2 mm < D ≤ 0.3 mm		2																			
	0.3 mm < D ≤ 0.5mm		1																			
	0.5 mm < D		0																			
	Total Q'ty		3																			
	<table><tr><th colspan="3">Size >= 5"</th></tr><tr><td colspan="2">Average Diameter</td><td>Qualified Qty</td></tr><tr><td colspan="2">D<0.25 mm</td><td>Ignored</td></tr><tr><td colspan="2">0.25 mm < D < 0.5 mm</td><td>3</td></tr><tr><td colspan="2">0.5 mm < D</td><td>0</td></tr></table>	Size >= 5"			Average Diameter		Qualified Qty	D<0.25 mm		Ignored	0.25 mm < D < 0.5 mm		3	0.5 mm < D		0						
	Size >= 5"																					
	Average Diameter		Qualified Qty																			
	D<0.25 mm		Ignored																			
	0.25 mm < D < 0.5 mm		3																			
	0.5 mm < D		0																			
Touch panel spot	<table><tr><th colspan="3">Size < 5"</th></tr><tr><td colspan="2">Average Diameter</td><td>Qualified Qty</td></tr><tr><td colspan="2">D < 0.2 mm</td><td>Ignored</td></tr><tr><td colspan="2">0.2 mm < D < 0.4 mm</td><td>5</td></tr><tr><td colspan="2">0.4 mm < D < 0.5 mm</td><td>2</td></tr><tr><td colspan="2">0.5 mm < D</td><td>0</td></tr></table>	Size < 5"			Average Diameter		Qualified Qty	D < 0.2 mm		Ignored	0.2 mm < D < 0.4 mm		5	0.4 mm < D < 0.5 mm		2	0.5 mm < D		0			
	Size < 5"																					
	Average Diameter		Qualified Qty																			
	D < 0.2 mm		Ignored																			
	0.2 mm < D < 0.4 mm		5																			
	0.4 mm < D < 0.5 mm		2																			
0.5 mm < D		0																				
Touch panel White line Scratch	<table><tr><th colspan="3">Size < 5"</th></tr><tr><td>Length</td><td>Width</td><td>Qualified Qty</td></tr><tr><td>-</td><td>W< 0.02</td><td>Ignored</td></tr><tr><td>L < 3.0</td><td>0.02 < W <0.05</td><td rowspan="2">2</td></tr><tr><td>L < 2.5</td><td>0.05 < W <0.08</td></tr><tr><td>-</td><td>0.08 < W</td><td>0</td></tr></table>	Size < 5"			Length	Width	Qualified Qty	-	W< 0.02	Ignored	L < 3.0	0.02 < W <0.05	2	L < 2.5	0.05 < W <0.08	-	0.08 < W	0				
	Size < 5"																					
	Length	Width	Qualified Qty																			
	-	W< 0.02	Ignored																			
	L < 3.0	0.02 < W <0.05	2																			
	L < 2.5	0.05 < W <0.08																				
-	0.08 < W	0																				

13 RELIABILITY TEST

NO.	TEST ITEM	TEST CONDITION
1	High Temperature Storage	80°C/120 hours
2	Low Temperature Storage	-30°C/120 hours
3	High Temperature Operating	70 °C /120 hours
4	Low Temperature Operating	-20°C/120 hours
5	High Temperature and High Humidity	Humidity 40°C, 90 %RH, 120 hours
6	Thermal Cycling Test (No operation)	-20°C for 30min, 70°C for 30 min. 100 cycles. Then test at room temperature after 1 hour
7	Vibration Test	Frequency :10~55 HZ; Stroke :1.5mm; Sweep:10HZ~55HZ~10HZ; 2 hours for each direction of X, Y, Z(6 hours for total)
8	Package Drop Test	Height: 60 cm 1 corner,3 edges,6 surfaces
9	ESD Test	± 2KV, Human body mode,100pF/1500Ω

Note 1. Sample quantity for each test item is 5 ~ 10 pcs.

Note 2. Before cosmetic and function test, the product must have enough recovery time, at least 2 hours at room temperature.

14 LEGAL INFORMATION

Riverdi grants the guarantee for the proper operation of the goods for a period of 12 months from the date of possession of the goods. If as a consequence of performing the obligation resulting from this guarantee the customer received a good free of defect instead of the defective good, then the period for the effectiveness of the guarantee shall commence anew from the moment the customer receives the good free of defects. Information about device is the property of Riverdi and may be the subject of patents pending or granted. It is not allowed to copy or disclosed this document without prior written permission.

Riverdi endeavors to ensure that the all contained information in this document is correct but does not accept liability for any error or omission. Riverdi products are in developing process and published information may be not up to date. Riverdi reserves the right to update and makes changes to Specifications or written material without prior notice at any time. It is important to check the current position with Riverdi.

Images and graphics used in this document are only for illustrative the purpose. All images and graphics are possible to be displayed on the range products of Riverdi, however the quality may vary. Riverdi is no liable to the buyer or to any third party for any indirect, incidental, special, consequential, punitive or exemplary damages (including without limitation lost profits, lost savings, or loss of business opportunity) relating to any product, service provided or to be provided by Riverdi, or the use or inability to use the same, even if Riverdi has been advised of the possibility of such damages.

Riverdi products are not fault tolerant nor designed, manufactured or intended for use or resale as on line control equipment in hazardous environments requiring fail-safe performance, such as in the operation of nuclear facilities, aircraft navigation or communication systems, air traffic control, direct life support machines or weapons systems in which the failure of the product could lead directly to death, personal injury or severe physical or environmental damage ('High-Risk Activities'). Riverdi and its suppliers specifically disclaim any expressed or implied warranty of fitness for High-Risk Activities. Using Riverdi products and devices in 'High-Risk Activities' and in any other application is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Riverdi from any and all damages, claims or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Riverdi intellectual property rights.

